

HOLE DOZER™ w/ CARBIDE TEETH HOLE SAW KITS

Description	Includes	Part No.
 12 PC HOLE DOZER™ w/ Carbide Teeth Hole Saw Kit	(1) 7/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-1/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-3/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-3/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2-1/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2-1/2" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 3/8" Small Thread Arbor (1) 7/16" Large Thread Quick Change Arbor (2) 1/4" x 3-1/2" Cobalt Pilot Bits	49-22-3090
 12 PC HOLE DOZER™ w/ Carbide Teeth Plumber's Hole Saw Kit	(1) 3/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 7/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-1/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-1/2" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-3/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2-1/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2-1/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2-5/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) Large Thread Arbor w/ Cobalt Pilot Bit (1) Small Thread Arbor w/ Cobalt Pilot Bit (2) Cobalt Pilot Bits	49-22-3091
 15 PC HOLE DOZER™ w/ Carbide Teeth Hole Saw Kit	(1) 3/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 7/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-1/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-1/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-3/8" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-1/2" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 1-3/4" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 2-9/16" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) 3" HOLE DOZER™ w/ Carbide Teeth Hole Saw (1) Large Thread Arbor w/ Cobalt Pilot Bit (1) Small Thread Arbor w/ Cobalt Pilot Bit (2) Cobalt Pilot Bits	49-22-3097

NEW

HOLE DOZER™ BI-METAL HOLE SAWS

OVERVIEW

MILWAUKEE® HOLE DOZER™ Bi-Metal Hole Saws new 3.5 TPI tooth design offers users the longest life in metal applications. These HOLE DOZER™ Bi-Metal Hole Saws feature the industry's only Lifetime Tooth Break Warranty and can take on all general purpose applications, making them the most durable hole saws. Our ALL ACCESS SLOTS solve the frustration of plug removal, making users more productive with less downtime between holes. The new slot design also gives users increased pilot visibility for accurate placement and faster chip ejection keeping their cut cool. HOLE DOZER™ Thermoset Coating allows for faster cutting and is optimized for cordless tools, delivering users 25% more holes per charge. MILWAUKEE® HOLE DOZER™ Bi-Metal Hole Saws are proudly made in the USA.

FEATURES

- Most Durable Hole Saw. Period.
- New 3.5 TPI Tooth Design
- ALL ACCESS SLOTS: Fast Plug Removal

HOLE DOZER™ BI-METAL HOLE SAWS

Size	Hanging Container	Shrink Wrap	With Arbor	Bulk
9/16"	49-56-0002	49-56-9690	–	–
5/8"	49-56-0012	49-56-9603	–	–
11/16"	49-56-0017	49-56-9604	–	–
3/4"	49-56-0023	49-56-9605	49-56-9658	49-56-5090 (25 pk)
13/16"	49-56-0027	49-56-9606	–	–
7/8"	49-56-0032	49-56-9607	49-56-9659	49-56-5100 (25 pk)
15/16"	49-56-0037	49-56-9608	–	–
1"	49-56-0043	49-56-9609	49-56-9662	49-56-5110 (25 pk)
1-1/16"	49-56-0047	49-56-9610	–	–
1-1/8"	49-56-0052	49-56-9611	49-56-9663	49-56-5120 (25 pk)
1-3/16"	49-56-0057	49-56-9612	–	49-56-5125 (25 pk)
1-1/4"	49-56-0062	49-56-9613	49-56-9664	49-56-5130 (25 pk)
1-5/16"	49-56-0067	49-56-9614	–	–
1-3/8"	49-56-0072	49-56-9615	49-56-9671	49-56-5140 (25 pk)
1-7/16"	49-56-0077	49-56-9616	–	–
1-1/2"	49-56-0082	49-56-9617	49-56-9665	49-56-5150 (25 pk)
1-9/16"	49-56-0087	49-56-9618	–	–
1-5/8"	49-56-0092	49-56-9619	–	49-56-5152 (25 pk)
1-11/16"	49-56-0097	49-56-9620	–	–
1-3/4"	49-56-0102	49-56-9621	49-56-9666	49-56-5155 (25 pk)
1-13/16"	49-56-0107	49-56-9622	–	–
1-7/8"	49-56-0112	49-56-9623	–	–
2"	49-56-0117	49-56-9624	49-56-9667	49-56-5160 (25 pk)
2-1/16"	49-56-0122	49-56-9625	–	–
2-1/8"	49-56-0127	49-56-9626	49-56-9668	49-56-5165 (25 pk)
2-1/4"	49-56-0132	49-56-9628	49-56-9680	49-56-5167 (25 pk)
2-5/16"	49-56-0137	49-56-9629	–	–

Size	Hanging Container	Shrink Wrap	With Arbor	Bulk
2-3/8"	49-56-0142	49-56-9630	–	–
2-1/2"	49-56-0147	49-56-9631	49-56-9669	49-56-5170 (25 pk)
2-9/16"	49-56-0153	49-56-9632	–	–
2-5/8"	49-56-0158	49-56-9633	–	49-56-5175 (16 pk)
2-11/16"	49-56-0159	49-56-9634	–	–
2-3/4"	49-56-0163	49-56-9635	–	–
2-7/8"	49-56-0167	49-56-9636	–	–
3"	49-56-0173	49-56-9637	49-56-9670	49-56-5180 (16 pk)
3-1/8"	49-56-0177	49-56-9638	–	–
3-1/4"	49-56-0183	49-56-9639	–	–
3-3/8"	49-56-0187	49-56-9640	–	–
3-1/2"	49-56-0193	49-56-9641	49-56-9682	49-56-5190 (9 pk)
3-5/8"	49-56-0197	49-56-9642	49-56-9683	49-56-5195 (9 pk)
3-3/4"	49-56-0203	49-56-9643	–	–
3-7/8"	49-56-0207	49-56-9644	–	–
4"	49-56-0213	49-56-9645	49-56-9685	49-56-5200 (9 pk)
4-1/8"	49-56-0217	49-56-9646	–	49-56-5205 (9 pk)
4-1/4"	49-56-0223	49-56-9647	49-56-9687	–
4-3/8"	49-56-0227	49-56-9648	–	–
4-1/2"	49-56-0233	49-56-9649	49-56-9689	–
4-3/4"	49-56-0237	49-56-9650	–	–
4-5/8"	49-56-0239	49-56-9627	–	–
5"	49-56-0243	49-56-9652	–	–
5-1/4"	49-56-0244	49-56-9653	–	–
5-1/2"	49-56-0247	49-56-9654	–	–
5-3/4"	49-56-0249	49-56-9655	–	–
6"	49-56-0253	49-56-9656	49-56-9698	–

