

Project Name

Location

Prepared By



## NUVO 65-556

LED FULL CUTOFF WALL PACK

### Notes

(pencil) 04/01/2023 03:45:12

### General

Status	Active
Fixture Type	Wall Pack
Finish	Bronze
Wattage	80W/100W/120W
Lumen Output	12107L-17789L
CCT (Kelvin)	3000K/4000K/5000K
Temperature	Soft White to Natural Light
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

### Specifications

Technology	LED
CRI	80+
Voltage	120V-347V
Beam Angle	106
Rated Hours	50000
Operating Temperature	-40C (-40F) to +50C (+122F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming
Photocell or Sensor	Yes - Bypassable
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 6KV
Weight (lb.)	9.74
Material	Die-Cast Aluminum

### Dimensions

Height (in.)	9.36
Width (in.)	13.28
Extension (in.)	8.11

### Compliance

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	S-CW1MVQ
B.U.G. Rating	B2-U0-G2
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Type A
Flicker Free	No

### Additional Information

Specification Note	Type II Light Distribution; For International Dark Sky Compliance the fixture CCT must be set to 3000K and installed in a downward facing and locked position
Warranty	5 Year Limited - Fixtures