



Color: ■ silver-colored

Technical data	
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	500 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Depth	0.09 mm
Marking surface	44 x 99 mm

Mechanical data	
Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	400 g
Fire load	0 MJ



Environmental requirements		
Ambient temperature (storage)		≤+21 °C
Ambient temperature (operation)		-40 ... +150 °C
Relative humidity		40 ... 50 %

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4050821632627
Customs tariff number		39199080888

Product classification		
UNSPSC		55121612

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search		
Environmental Product Compliance 210-804		

Documentation

Operating Instructions			
210-804 Information on handling print material	1 28.08.2020	pdf 1347.39 KB	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking device



Item No.: 258-5000
Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi; With marking material