

Project Name

Location

Prepared By

**SATCO S9599**

12W/LED/5-6"TRIM/2700K/120V/2P

**Notes**

(www) 05-13-2023 23:26:43

**General**

Status	Discontinued
Substitute	S29599
Recessed Can Size	5-6 in.
Wattage	12W
Voltage	120V
Finish	White
CCT (Kelvin)	2700K
Color Temperature	Soft White
Lumen Output	800L
Indoor or Outdoor Fixture	Indoor

**Specifications**

Technology	LED
CRI	80+
Beam Angle	110
Rated Hours	25000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable

**Dimensions**

Width (in.)	7.48
Height (in.)	6.3
Weight (lb.)	0.43

**Compliance**

Safety Listing	cETLus - Classified
Location Rating	Damp
ENERGY STAR	No
DLC Approved	No
California Status	Non-Compliant
Title 20 / 24 Status	Non-Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

**Additional Information**

Additional Information	Adjustable neck length from 4.47 in. to 6.30 in.
Installation Notes	Fits 5-6 in. Recessed Cans
Warranty	5-Years