


NON INSULATED FERRULES DIN 46228/1



Technical Information

Material: E-Copper,
Surface electro tinned.
Minimum Coating Thickness 3µm.
Rated at 600V Max
Tolerances: after part 1



B

Non-Insulated Ferrules

Rated at 600V

Part-No.	AWG	Size mm ²	d1	d2	l	s	Packing Unit	Approved Tool V Series	CRIMP TOOLS			
									RAT-FER	SPR-FER	RAT-FER2	RAT-FER2XL
FERN-20-10M	20	0.75	1.20	2.30	10.00	0.15	1	V915	•	•		
FERN-18-10M	18	1.00	1.40	2.50	10.00	0.15	1	V915	•	•		
FERN-16-10M	16	1.50	1.70	2.80	10.00	0.15	1	V915	•	•		
FERN-14-10M	14	2.50	2.20	3.40	10.00	0.15	1	V915	•	•		
FERN-12-12M	12	4.00	2.80	4.00	12.00	0.20	1	V915	•	•		
FERN-10-12B	10	6.00	3.50	4.70	10.00	0.20	250	V915	•	•	•	
FERN-8-12B	8	10.00	3.50	4.70	12.00	0.20	250	V925	•	•	•	
FERN-6-12B	6	16.00	4.50	5.80	12.00	0.20	250	V925			•	
FERN-4-12B	4	25.00	7.30	9.50	12.00	0.20	250	V940				•
FERN-2-12C	2	35.00	8.30	11.00	12.00	0.20	100	V940				•
FERN-1/0-18C	1/0	50.00	10.30	13.00	18.00	0.30	100	V945				
FERN-2/0-25C	2/0	70.00	12.50	15.00	25.00	0.40	100	V945				
FERN-3/0-25L	3/0	95.00	14.50	17.00	25.00	0.40	50	V945				
FERN-4/0-32L	4/0	120.00	16.50	19.00	32.00	0.50	50	V950 tool w/V953 die				

For Copper Stranded Wire Only

See Page E-5 for tools.

INSULATED FERRULES IN CUT-STRIP FORM

Technical Information

Insertion Funnel is made of Polypropylene and is heatresistant up to 105 Deg. C.
Material: E-Copper,
Surface electro tinned.
Minimum Coating Thickness 3µm.
Rated at 600V Max
Tolerances: after part 4



Cut-Strips Polypropylene Insulated Ferrules

Rated at 600V Max, 105°C

Colour DIN	Part-No.	AWG	Size mm ²	d1	d2	l1	l2	s1	s2	a1	a2	a3	a4	Packing Unit	Approved Tool
	FERSTR-22WH	22	0.50	1.00	2.60	14.00	8.00	0.15	0.30	0.20	3.60	0.25	1.50	500(10x50)	SPR-JOK
	FERSTR-20GR	20	0.75	1.20	2.80	14.00	8.00	0.15	0.30	0.20	3.60	0.25	1.50	500(10x50)	SPR-JOK
	FERSTR-18RD	18	1.00	1.40	3.00	14.00	8.00	0.15	0.30	0.20	4.20	0.25	1.50	500(10x50)	SPR-JOK
	FERSTR-16BK	16	1.50	1.70	3.50	14.00	8.00	0.15	0.30	0.20	4.20	0.25	1.50	500(10x50)	SPR-JOK
	FERSTR-14BL	14	2.50	2.20	4.20	14.00	8.00	0.15	0.30	0.20	5.00	0.25	1.50	500(10x50)	SPR-JOK

For Copper Stranded Wire Only

See Page E-7 for tools.

