




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CFFPL4**	.24 LB/10 PCS (110.3 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [ ] ARE IN METRIC.
4. FACEPLATE ACCEPTS 4 MINI-COM MODULES.
5. FACEPLATE COMES WITH LABEL AND LABEL COVER.
6. FACEPLATE SNAPS INTO STANDARD FURNITURE OPENING. (1.375 X 2.710) MAX PANEL THICKNESS: .09" [ 2.29MM ].



PART NUMBER		CFFPL4**	
TITLE			
MINI-COM 4 POSITION FURNITURE FACEPLATE WITH LABEL COVER			
CUSTOMER DRAWING			
ITEM REVISION NAME		M00719BC/12	
DATASET FILE NAME		M00719BC_DC02/12A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .xx ± .03 [ .8 ]		ABS	
.xxx ± .010 [ .3 ]		DRAWING NUMBER:	
ANGLES ±		00719-02	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	8-11-99	MECA	NONE
REV	DATE	BY	CHK
5	5/25/21	BJN	MDJR
4	3/19/14	JSP	REFR

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	5/25/21	BJN	MDJR	MMR	VERTICAL DIMENSION TO BOTTOM OF FACEPLATE, NOT LATCH	00719-02
4	3/19/14	JSP	REFR	MMR	REVISED AND REDRAWN, PREVIOUS REVISIONS HAVE BEEN OMITTED.	00719-02

D101000DA/14