

12" & 18" HIGH VELOCITY FLOOR FANS



Enjoy Better Air Circulation with our High-Performing Fan. It Delivers Powerful, Consistent Airflow with Adjustable Speeds, Ensuring Comfort in any Space.

FEATURES

- 3 Speed Button Control
- Powder-Coated Black Painted Finish
- All Metal Frame & Housing
- Aluminum Blades
- Dual Ball Bearing Motor
- Adjustable Tilt for Pin-Point Accuracy
- Includes Wall Mounting Bracket
- Convenient Carrying Handle
- Cord Wrap
- OSHA Guard
- 6' Power Cord
- 12" & 18" Sizes Available

Wall Mounted
Bracket



Push Button
Control



Wall
Mounted



MODEL	SIZE	DESCRIPTION	DIMENSIONS	CFM	VOLTS	WATT	AMPS	WEIGHT
FF12-B	12"	3 Speed, Push Button Control	15.55" x 7.48" x 15.75"	1,560	120	50	0.4	5.86 LBS
FF18S-B	18"	3 Speed, Push Button Control	21.26" x 9.45" x 21.06"	4,012	120	100	0.87	9.92 LBS