

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L3 R6, and L3R R6.

CONSTRUCTION

White finish has integral flange.

Black baffle finish has polymeric flange ring as standard.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTING

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.

WARRANTY

Fixtures are covered by Lithonia Lighting 24-month warranty against mechanical defects in manufacture.

Catalog Number
Notes
Type

Contractor Select Incandescent

4" Trims


IC/Non IC
New Construction
Remodel




3E1



3B1W/3B1



3E1



3B1W/3B1

All dimensions are inches (centimeters).

ORDERING INFORMATION

Must be ordered in standard carton quantity multiples.

Catalog Number	UPC	Description	Max Lamp Wattages	Size	Color	Type	Pallet Qty.	Standard Carton Qty.
3B1W R24	745975234264	4" trim	IC: 35 PAR20; Non-IC: 50 Par20	Narrow	White	Baffle	786	24
3B1 R12	745975234295	4" trim	IC: 35 PAR20; Non-IC: 50 Par20	Narrow	Black	Baffle	1344	12
3E1 R6	745973752937	4" trim	IC: 35 PAR20; Non-IC: 50 R20, 50 Par20	Narrow	White	Eyeball	756	6
3B2W R12	745975281015	4" trim	Non-IC: 50 Par20, 50 R20	Narrow	White	Baffle	1344	12

4" Trims

Description Catalog number	Maximum wattage Sheet number
-------------------------------	---------------------------------

General/Task

Baffle Narrow Flange		
3B1	Black	
3B1W	White	
<i>IC</i>		35 PAR20
<i>Non IC</i>		50 PAR20
<i>IC/Non IC</i>		RBAF-230

Baffle Deep Narrow Flange		
3B2W	White	
<i>IC</i>		30 R20 35 PAR20
<i>Non IC</i>		50 R20
		ROPN-280

Accent/Wallwash

Eyeball Narrow Flange		
3E1	White	
<i>IC</i>		35 PAR20
<i>Non IC</i>		50 PAR20 50 R20
<i>IC/Non IC</i>		RADJ-210