Specifications



APC Smart-UPS C, Line Interactive, 1000VA, Rackmount 2U, 120V, 6x NEMA 5-15R outlets, SmartConnect port, USB and Serial communication, AVR,Graphic LCD

SMC1000-2UC

Product availability: Non-Stock - Not normally stocked in distribution facility

Overview

Lead time

Main

Product or Component Type

Uninterruptible power supply (UPS)

Usually Ships within 2 Weeks

Complementary

Communication port type	SmartConnect Ethernet port
Software package	SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph 🖸
Efficiency	View Efficiency Graph 🗗
Battery Type	Lead-Acid battery
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	46 year(s)
Replacement battery	APCRBC124
Battery Charge Power (Watts)	72 W rated

General

Provided equipment	Documentation CD Installation guide Rack Mounting brackets USB cable
Number of power module	0
Number of power module filled	0

slots

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number of power module free slots	0
product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

3	
Number of rack unit	2U
Cable length	8 ft (2.4 m)
Number of cables	1
color	Black
Height	3.39 in (8.6 cm)
Width	17.01 in (43.2 cm)
Depth	15.98 in (40.6 cm)
Net Weight	45.24 lb(US) (20.52 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Input Connection Type	NEMA 5-15P
Efficiency at full load	85136 V adjustable 93130 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Kw Rating	600 W
rated power in VA	1000 VA
output connection type	6 NEMA 5-15R
Harmonic distortion	Less than 5%
Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	600 W
Transfer Time	6ms typical : 10ms maximum
Тороlоду	Line Interactive
Waveform Type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	cULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000

Environmental

41 dBA
175 Btu/h
010000 ft
32104 °F (040 °C)
5113 °F (-1545 °C)
050000 ft (015240 m)
095 %
095 %

Communications & Management

control panel	Multi-function LCD status and control console
Free slots	0
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304322733
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.25 in (23.5 cm)
Package 1 Width	22.44 in (57 cm)
Package 1 Length	21.06 in (53.5 cm)
Package 1 Weight	45.66 lb(US) (20.71 kg)

Contractual warranty

Warranty

2 years repair or replace

Lenvironmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability \geq

\mathcal{Q} Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	923
Environmental Disclosure	Product Environmental Profile

Use Better

S Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	B2b22a56-41f2-497e-9ea6-cf093b3b8bd3
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
ℰ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

\odot Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes

Product data sheet SMC1000-2UC

Image of product / Alternate images

Alternative





