

TEW Bare Copper

CSA/UL

Conductor	Bare copper	
Insulation	600V Colour coded PVC	
Temperature	-30°C to 105°C	
Approvals	Certified to CSA standard C22.2 No. 127 Equipment/Lead Wires UL recognized AWM as per subject 758 Passes CSA/FT1 vertical flame test Passes UL-VW-1 vertical flame test UL Style 1015/1230	
Applications	For use in internal wiring of electrical and electronic equipment, point to point wiring, and internal wiring of panels and meters.	
Packaging	X 150, X 300, X 1500 m , Barrel packs	

Product Code	AWG Size	Stranding	Insulation Thickness (inches)	Nominal O.D. (inches)	Cable Weight (lbs/mft)
34A1801	18	Solid	0.030	0.104	9
34A1601	16	Solid	0.030	0.113	13
34A1401	14	Solid	0.030	0.126	19
34A2207	22	7	0.030	0.093	6
34A2010	20	10	0.030	0.100	7
34A1816	18	16	0.030	0.108	10
34A1626	16	26	0.030	0.122	13
34A1441	14	41	0.030	0.137	19
34A1265	12	65	0.030	0.159	27
34A10104	10	104	0.030	0.183	41
34A08168	8	165	0.045	0.295	68
34A06266	6	266	0.060	0.335	116

TEW_BC.pdf