

Breaker BQD 3P 35A 347/600VAC 10kA CSA

product function note			
number of poles	3		
suitability for operation	CONSTRUCTION		
Electricity			
continuous current rated value	35 A		
supply voltage frequency rated value 50/60 Hz	Yes		
Environmental conditions			
ambient temperature during operation maximum	40 °C		
Model			
product brand name	Siemens		
special product feature	PANELBOARD MOUNT		
type of electrical connection	LOW TAB		
Mechanical Design			
depth [in]	3 in		
design of the overload release	THERMAL MAGNETIC TRIP UNIT		
design of the product	BQD		
height [in]	5 in		
material of the enclosure	MOLDED CASE CIRCUIT BREAKER		
size of the circuit-breaker	100A		
width [in]	3 in		
General product approval			
standard	UL 489 CSA-C22.2		
General Product Approval		EMV	other



[Miscellaneous](#)



[Confirmation](#)

other	Environment		
Miscellaneous	Miscellaneous	Environmental Con- firmations	

last modified: 12/20/2023

