



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 2-Pole, 120/240VAC are Circuit Protection Molded Case Circuit Breakers. Type: BLH Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240V Amperage Rating: 90A Trip Range: Thermal Magnetic Interrupt Rating: 22 AIC Number Of Poles: 2P

| product function note          |                         |
|--------------------------------|-------------------------|
| number of poles                | 2                       |
| suitability for operation      | Electrical Distribution |
| Electricity                    |                         |
| continuous current rated value | 90 A                    |
| Model                          |                         |
| product brand name             | Siemens                 |
| type of electrical connection  | BOLT-ON                 |
| Mechanical Design              |                         |
| depth [in]                     | 4 in                    |
| design of the product          | BLH                     |
| height [in]                    | 2 in                    |
| width [in]                     | 4 in                    |
| General product approval       |                         |
| standard                       | UL 489                  |

last modified:

12/20/2023

