

M18™ FORCE LOGIC™ 2" - 3" ProPEX® Expansion Tool Kit

2633-22HD

Specifications:

Capacity	2", 2-1/2" and 3"
Auto-Rotation	Built-In
Auto-Cycle	Built-In
Dimensions (L x W x H)	14.5" x 11.8" x 4.8"
Weight	13.1 lbs



Includes: (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, (3) ProPEX® Expansion Heads (1/2", 2-1/2", 3"), Side Handle, Grease, Multi-Voltage Charger, Carrying Case

Related Accessories:
49-08-2401 150g ProPEX® Expander Cone Grease;
49-16-2614 2" ProPEX® Expansion Head;
49-16-2616 2-1/2" ProPEX® Expansion Head;
49-16-2618 3" ProPEX® Expansion Head



M18™ ProPEX® Expansion Tool Kit

2632-22XC (2632-20 Tool-Only)

Specifications:

Capacity	3/8" – 1-1/2"
Auto-Rotation	Built-In
Dimensions (L x W x H)	8.7" x 4.4" x 10.8"
Weight	9.2 lbs



Includes: (2) M18™ REDLITHIUM™ XC3.0 Battery Packs, (3) ProPEX Expansion Heads (1", 1-1/4", 1-1/2"), Grease, Multi-Voltage Charger, Carrying Case

Related Accessories:
49-08-2400 ProPEX® Expander Cone Grease;
49-16-2608 1" ProPEX® Expansion Head;
49-16-2610 1-1/4" ProPEX® Expansion Head;
49-16-2612 1-1/2" ProPEX® Expansion Head

M18 FUEL SWITCH PACK™ Sectional Drum System Kit

2775-211, 2775A-211, 2775B-211, 2775C-222, 2775E-211

Specifications:

Maximum Drain Line Capacity	1-1/4" – 4" up to 100' (not for roots)
Drum Capacity	Inner Core Cables: 5/16" x 75', Best For 1-1/4" – 2-1/2" drain lines; 3/8" x 50', Best For 2" – 3" drain lines; 1/2" x 50', Best For 3" – 4" drain lines Open Wind Cables: 5/8" x 50', Best For 1-1/4" – 3" drain lines (soft blockages)
Backpack Straps	Yes
Removable Drum	Yes, Tool-Free
Cable Spin Speed	250 RPM
Electronic Foot Pedal	Yes
Integrated Drum Brake	Yes
Length	15.8"



Includes: **2775A-211:** 5/16" x 75' Inner Core Drop Head Cable w/ RUST GUARD™ Plating;
2775B-211: 3/8" x 50' Inner Core Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1-1/2" Spade Bit, 1-1/2" C-Cutter, Medium Funnel, Medium Drop Head), Pin Key;
2775C-222: Additional M18™ REDLITHIUM™ XC5.0 Battery Pack, Additional SWITCH PACK™ Drum w/ Anchor Cable, (2) 1/2" x 50' Inner Core Coupling Cables w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1-1/2" Spade Bit, 1-1/2" C-Cutter, Medium Funnel, Medium Drop Head), Pin Key;
2775E-211: 5/8" x 50' Open Wind Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Head Attachments w/ RUST GUARD™ Plating (1" Spade Bit, 1" C-Cutter, Small Bulb Head, Small Drop Head), Pin Key;
All Kits Include: **2775-211:** SWITCH PACK™ Powered Base, SWITCH PACK™ Drum w/ Anchor Cable, (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Multi-Voltage Charger



Related Accessory:
47-53-2775 SWITCH PACK™ Drum w/ Anchor Cable

M18 FUEL Drain Snake w/ CABLE DRIVE™ Locking Feed System Kit

2772A-21, (2772A-20 Tool-Only), 2772B-21XC

Specifications:

Maximum Drain Line Capacity	1-1/4" – 3" up to 50'
Drum Capacity	1/4" x 50', Best For 1-1/4" – 2" drain lines; 5/16" x 50', Best For 1-1/4" – 2-1/2" drain lines; 3/8" x 35', Best For 2" – 3" drain lines
Powered Cable Feed & Retract	Yes, CABLE-DRIVE™
Variable Feed Speed	0 – 8" Per Second
Variable Spin Speed	0 – 600 RPM
Feed Lock	Yes, Twist Lock
Cable Lock	Yes, Twist Lock
LED Light	Yes
Length / Weight	19.5" / 8.2 lbs



Includes: **2772A-21** (1) M18™ REDLITHIUM™ CP2.0 Battery Pack, 5/16" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating;
2772B-21XC (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, 1/4" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating, 3/8" x 35' Inner Core Coupling Cable w/ RUST GUARD™ Plating, (4) Cable Attachments (1" Spade Bit, 1" C-Cutter, Small Bulb Head, Small Drop Head), Pin Key;
All Kits Include: Multi-Voltage Charger, Storage Bucket

2772A-20 Includes 5/16" x 35' Inner Core Bulb Head Cable w/ RUST GUARD™ Plating, Battery and Charger Sold Separately



MILWAUKEE® Drain Cleaning Accessories

Compatible with MILWAUKEE® and other professional brand drain cleaning machines

RUST GUARD™ Plated Cables

48-53-2563 1/4" x 25' Inner Core Bulb Head Cable;
48-53-2564 1/4" x 25' Inner Core Drop Head Cable;
48-53-2671 1/4" x 35' Inner Core Bulb Head Cable;
48-53-2672 1/4" x 50' Inner Core Bulb Head Cable;
48-53-2561 5/16" x 25' Inner Core Bulb Head Cable;
48-53-2562 5/16" x 25' Inner Core Drop Head Cable;
48-53-2673 5/16" x 35' Inner Core Bulb Head Cable;
48-53-2674 5/16" x 50' Inner Core Bulb Head Cable;
48-53-2772 5/16" x 75' Inner Core Drop Head Cable;
48-53-2676 3/8" x 25' Inner Core Coupling Cable;
48-53-2675 3/8" x 35' Inner Core Coupling Cable;
48-53-2773 3/8" x 50' Inner Core Coupling Cable;
48-53-2774 1/2" x 50' Inner Core Coupling Cable;
48-53-2775 5/8" x 50' Open Wind Coupling Cable

RUST GUARD™ Plated Cable Attachments

Compatible with MILWAUKEE® Coupling Cables

48-53-2681 Small Bulb Head;
48-53-2682 Small Drop Head;
48-53-2683 1" Spade Bit;
48-53-2684 1" C-Cutter;
48-53-2685 5 Pc Small Cable Head Attachment Kit;
48-53-2786 Funnel Head;
48-53-2787 Medium Drop Head;
48-53-2788 1-1/2" Spade Bit;
48-53-2789 1-1/2" C-Cutter;
48-53-2790 5 Pc Medium Cable Head Attachment Kit

M18™ Transfer Pump Kit

2771-21 (2771-20 Tool-Only)

Specifications:

Gallons Per Hour	480
Gallons Per Battery (XC3.0)	144
Maximum Lift	18'
Maximum Head Height	75'
Self-Priming	Yes
Flexible Impeller	Yes
Fittings	3/4" Brass Inlet and Outlet
Weight	7.5 lbs



Includes: (1) M18™ REDLITHIUM™ XC3.0 Battery Pack, (2) 3/4" Brass Fittings, Multi-Voltage Charger

M18™ 2-Speed Grease Gun Kit

2646-22CT, 2646-21CT (2646-20 Tool-Only)

Specifications:

Output Pressure	Up to 10,000 PSI (690 BAR)
Run-Time	Up to 10 Cartridges Per Charge
Grease Capacity	14 oz Cartridge, 16 oz Bulk, 16 oz Suction
Air Bleeder Valve	Yes
Weight	8.5 lbs



Includes: **2646-22CT** (2) M18™ REDLITHIUM™ CP1.5 Battery Packs;
2646-22CT (1) M18™ REDLITHIUM™ CP1.5 Battery Pack;
All Kits Include: 48" Flex Hose with Spring Guard, High Pressure Grease Coupler, Shoulder Strap, Multi-Voltage Charger, Carrying Case

Related Accessories:
49-16-2646 M18™ Grease Gun 400g Clear Barrel;
49-16-2647 M18™ Replacement Grease Gun Hose with High Pressure Coupler;
49-16-2648 M18™ Right Angle Grease Gun Coupler;
49-16-2649 M18™ High Pressure Grease Coupler (2-Pack)



M18™ 10 oz Caulk and Adhesive Gun Kit

2641-21CT (2641-20 Tool-Only)

Specifications:

Force	950 lbs
Inches Per Minute	0 – 21
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.8 lbs



Includes: (1) M18™ REDLITHIUM™ CP1.5 Battery Pack, 10 oz Carriage, M18™ 10 oz Plunger Rod and Piston Assembly, Multi-Voltage Charger