

M18 BRUSHLESS SINGLE ACTION MINI HYDRAULIC PUMP

Force Output (bar)	700(10,000 psi)
Oil Delivery Low Pressure(l/min)	0.3
Oil Delivery High Pressure(l/min)	0.2
Oil Capacity (L)	1.0
Weight w/12.0Ah Battery Pack(kg)	6.6

M18 HMP700



NEW

ACCESSORIES

129227516 1 Liter Can Of Hydraulic Oil



M18 FORCE LOGIC 125MM UNDERGROUND CABLE CUTTER

Voltage	18V
Cutting Range(CU/AL/SWA) (mm)	125
Head Rotation(°)	180
Output Force (tons)	13
Weight w/ 8.0Ah Battery Pack(kg)	15.9

M18 HCC125R



NEW



M18 FORCELOGIC STRUT SHEAR

Battery System	M18
Strut material	Mild steel, Galvanized steel
Max material thickness (mm)	3
Force (kN)	176.4
Cutting Cycle	5 seconds
Dual LEDs	YES
Tri-Stand Chain Vice Mount	YES
Die Retention Arm	YES
Tool dimension (mm)	444.5 x 193.8 x 243.6
Weight (Tool only) (kg)	10.7

M18 STS0



NEW

ACCESSORIES

49-16-0158	Strut Shearing Dies 41mm X 41mm
49-16-1316	Strut Shearing Dies 21mm X 41mm
49-16-0078	Strut Shearing Dies 22mm X 41mm
49-16-1513	Strut Shearing Dies 21mm X 41mm Combo
49-16-1578	Strut Shearing Dies 22mm X 41mm Combo



M18

M18 FORCE LOGIC 15T CRIMPER

Material Composition	Reinforced Nylon
Length (inch)	4.53
Weight (lb)	16.85
Height (inch)	6.69
Width (inch)	26.5
Force (tons)	15
Capacity Cu	#8AWG - 1500 MCM Cu
Capacity Al	#8AWG - 1250 MCM Al

M18 HCCT15



ACCESSORIES

15T P-Dies (750MCM)

4915P750C	Conductor Type - Copper
4915P750	Conductor Type - Aluminum

15T P-Dies (800MCM)

4915P800C	Conductor Type - Copper
4915P800	Conductor Type - Aluminum

15T P-Dies (1000MCM)

4915P000C	Conductor Type - Copper
4915P000	Conductor Type - Aluminum

15T P to U-Die Adapter

49-15-PUAD	15T P to U-Die Adapter
------------	------------------------

