

M18 FUEL

Pipe Threader
w/ ONE-KEY™ Kit

2874-22HD

Specifications:

Capacity	1/8" – 2"
Kickback Control	AUTOSTOP™
Threading Support Arm	Yes
Trigger	Variable Speed
Die Head Retention Lock	Yes
Die Head Compatibility	RIDGID® 12R, Reed R12+

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Packs, Threading Support Arm, Rapid Charger, Carrying Case





M18™ FORCE LOGIC™
Long Throw Press Tool Kit

2773-22L (2773-20L No Jaw Kit)

Specifications:

Capacity	1/2" – 4" (Varies by Material)
Calibration Interval	50,000 Cycles (LED Indicator)
Approximate Cycle Time	4 Seconds, 8 Seconds at Extended Stroke
Press Force	7,200 lbs
Length / Weight	20.1" / 10.1 lbs

Includes: 2773-22L (2) M18™ REDLITHIUM™ XC3.0 Battery Packs, (3) Jaws (1/2", 3/4", 1"), Multi-Voltage Charger, Carrying Case; 2773-20L No Jaws Included



M18™ Short Throw Press Tool
w/ PEX Crimp Jaws Kit

2674-22C, 2674-20C

Specifications:

Capacity	Up to 1"
Cycle Time	3 Seconds
Auto Cycle	Yes
Length / Weight	13.5" / 4.8 lbs

Includes: 2674-22C (2) M18™ REDLITHIUM™ CP2.0 Battery Packs, Multi-Voltage Charger; 2674-20C Battery and Charger Sold Separately; **All Kits Include:** (3) PEX Crimp Jaws (1/2", 3/4", 1"), Carrying Case



M18™ FORCE LOGIC™ 2" - 3"
ProPEX® Expansion Tool Kit

2633-22HD

Specifications:

Capacity	2", 2-1/2" and 3"
Auto-Rotation	Built-In
Auto-Cycle	Built-In
Dimensions (L x W x H)	14.5" x 11.8" x 4.8"
Weight	13.1 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC8.0 Battery Packs, (3) ProPEX® Expansion Heads (2", 2-1/2", 3"), Side Handle, Grease, Multi-Voltage Charger, Carrying Case

Related Accessories:
49-08-2401 150g ProPEX® Expander Cone Grease
49-16-2614 2" ProPEX® Expansion Head
49-16-2616 2-1/2" ProPEX® Expansion Head
49-16-2618 3" ProPEX® Expansion Head



REDLITHIUM
HIGH OUTPUT XC8.0



M18™ FORCE LOGIC™
Press Tool Kit
w/ ONE-KEY™
with 1/2" - 2" CTS Jaws

2922-22 (2922-20 No Jaw Kit)

Specifications:

Capacity	1/2" – 4" (Varies by Material)
Calibration Interval	50,000 Cycles
Approx Cycle Time	4 Seconds
Press Force	7,200 lbs
ONE-KEY™ Compatible	Report. Track. Manage.
Performance Reporting	Wireless, Mobile, Desktop
Length/Weight	14.1" / 6.5 lbs

Includes: (2) M18™ REDLITHIUM™ CP2.0 Battery Packs, (6) CTS Jaws (1/2", 3/4", 1", 1-1/4", 1-1/2", 2"), Multi-Voltage Charger, Carrying Case; 2922-20 No Jaws Included



FORCE LOGIC™ Press Tool
Accessories

Compatible with 2922-20 and 2773-20L

Accessory Kits

49-16-2696 1/2" – 1" IPS-P Press Jaw Kit
49-16-2690 2-1/2" – 4" CTS-Vr1 Press Ring Kit
49-16-2691* 1-1/4" – 2" IPS-Ar1 Press Ring Kit
49-16-2697 1/2" – 2" IPS-P Press Ring Kit
49-16-2698* 2-1/2" – 4" IPS-Pr2 Press Ring Kit

CTS Jaws & Rings

49-16-2650 1/2" CTS-V Press Jaw
49-16-2651 3/4" CTS-V Press Jaw
49-16-2652 1" CTS-V Press Jaw
49-16-2653 1-1/4" CTS-V Press Jaw
49-16-2654 1-1/2" CTS-V Press Jaw
49-16-2655 2" CTS-V Press Jaw
49-16-2656 2-1/2" CTS-Vr1 Press Ring
49-16-2657 3" CTS-Vr1 Press Ring
49-16-2658 4" CTS-Vr1 Press Ring

IPS Jaws & Rings

49-16-2650B 1/2" IPS-P Press Jaw
49-16-2651B 3/4" IPS-P Press Jaw
49-16-2652B 1" IPS-P Press Jaw
49-16-2653B 1-1/4" IPS-Pr1 Press Ring
49-16-2654B 1-1/2" IPS-Pr1 Press Ring
49-16-2655B 2" IPS-Pr1 Press Ring
49-16-2656B* 2-1/2" IPS-Pr2 Press Ring
49-16-2657B* 3" IPS-Pr2 Press Ring
49-16-2658B* 4" IPS-Pr2 Press Ring
49-16-2650S 1/2" IPS-IA Press Jaw
49-16-2651S 3/4" IPS-IA Press Jaw
49-16-2652S 1" IPS-IA Press Jaw
49-16-2653S 1-1/4" IPS-IAr2 Press Ring
49-16-2654S* 2" IPS-IAr2 Press Ring
49-16-2655S* 2" IPS-IAr2 Press Ring

PEX Jaws & Rings

49-16-2651C 1/2" PEX-CRIMP Jaw
49-16-2653C 3/4" PEX-CRIMP Jaw
49-16-2654C 1" PEX-CRIMP Jaw
49-16-2655C 1-1/4" PEX-CRIMP Jaw
49-16-2656C 1-1/2" PEX-CRIMP Jaw
49-16-2657C 2" PEX-CRIMP Jaw

*Compatible with 2773-20L only.

ACR Jaws & Rings

49-16-2650M 1/4" Streamline™ ACR Press Jaw
49-16-2652M 3/8" Streamline™ ACR Press Jaw
49-16-2653M 1/2" Streamline™ ACR Press Jaw
49-16-2654M 5/8" Streamline™ ACR Press Jaw
49-16-2655M 3/4" Streamline™ ACR Press Jaw
49-16-2656M 7/8" Streamline™ ACR Press Jaw
49-16-2651M 1-1/8" Streamline™ ACR Press Ring
49-16-2661M 1/4" – 7/8" Streamline™ ACR Press Jaw Kit
49-16-2650R 1/4" RLS® Press Jaw
49-16-2652R 3/8" RLS® Press Jaw
49-16-2653R 1/2" RLS® Press Jaw
49-16-2654R 5/8" RLS® Press Jaw
49-16-2655R 3/4" RLS® Press Jaw
49-16-2656R 7/8" RLS® Press Jaw
49-16-2657R 1-1/8" RLS® Press Jaw
49-16-2658R 1-3/8" RLS® Press Jaw
49-16-2660R 1/4" – 1-3/8" RLS® Press Jaw Kit



M18™ Short Throw Press Tool
w/ Viega® PureFlow® Jaws Kit

2674-22P, 2674-20P

Specifications:

Capacity	Up to 1"
Cycle Time	3 Seconds
Auto Cycle	Yes
Length / Weight	13.5" / 4.8 lbs

Includes: 2674-22P (2) M18™ REDLITHIUM™ CP2.0 Battery Packs, Multi-Voltage Charger; 2674-20P Battery and Charger Sold Separately; **All Kits Include:** (3) Viega® PureFlow® Jaws (1/2", 3/4", 1"), Carrying Case



Short Throw
Press Tool Accessories

Compatible with 2674-20C and 2674-20P

49-16-2630C 3/8" PEX Crimp Jaw
49-16-2631C 1/2" PEX Crimp Jaw
49-16-2632C 5/8" PEX Crimp Jaw
49-16-2633C 3/4" PEX Crimp Jaw
49-16-2634C 1" PEX Crimp Jaw
49-16-2630P 3/8" Viega® PureFlow® Jaw
49-16-2631P 1/2" Viega® PureFlow® Jaw
49-16-2632P 5/8" Viega® PureFlow® Jaw
49-16-2633P 3/4" Viega® PureFlow® Jaw
49-16-2634P 1" Viega® PureFlow® Jaw

M18™ ProPEX®
Expansion Tool Kit

2632-22XC (2632-20 Tool-Only)

Specifications:

Capacity	3/8" – 1-1/2"
Auto-Rotation	Built-In
Dimensions (L x W x H)	8.7" x 4.4" x 10.8"
Weight	9.2 lbs

Includes: (2) M18™ REDLITHIUM™ XC3.0 Battery Packs, (3) ProPEX® Expansion Heads (1", 1-1/4", 1-1/2"), Grease, Multi-Voltage Charger, Carrying Case

Related Accessories:
49-08-2400 ProPEX® Expander Cone Grease
49-16-2608 1" ProPEX® Expansion Head
49-16-2610 1-1/4" ProPEX® Expansion Head
49-16-2612 1-1/2" ProPEX® Expansion Head

