

PERFORMANCE

MAXIMUM COMFORT.
LONGEST LASTING.

Robust, Durable Cap
Abrasion resistant

Durable Metal Rivets

Pressure Reducing Foam

Layered Gel Zone
Absorbs pressure & supports knee

Dual Material Lower Strap

1680D Ballistic Nylon

Also Available:

Non-Marring Performance Knee Pads
48-73-6040

Model #	Description
48-73-6030	Performance Knee Pads
48-73-6040	Non-Marring Performance Knee Pads

Robust Durable Cap

STABILIZER PERFORMANCE

MOST SECURE.
MAXIMUM COMFORT.

Large Flat Cap
Increased stability

Hinged Thigh Strap
Better mobility

Layered Gel Zone
Absorbs pressure & supports knee

Pressure Reducing Foam

Dual Material Lower Strap

1680D Ballistic Nylon

Durable Metal Rivets

Model #	Description
48-73-6050	Stabilizer Performance Knee Pads

Large Flat Cap for Increase Stability

LOCKING TOOL LANYARDS

BEST SHOCK
ABSORPTION

ANSI/ISEA
121-18

Integrated Swivel

Color Coded
Easy weight identification

Individualized Serial Numbers
Inventory management

Double-Locking Carabiner

Part #	Weight Rating	Description
48-22-8810	10 lbs	10 lbs Locking Tool Lanyard
48-22-8811	10 lbs	10 lbs 54" Extended Reach Locking Tool Lanyard
48-22-8812	10 lbs	10 lbs 72" Extended Reach Locking Tool Lanyard
48-22-8815	15 lbs	15 lbs Locking Tool Lanyard
48-22-8816	15 lbs	15 lbs 54" Extended Reach Locking Tool Lanyard
48-22-8817	15 lbs	15 lbs 72" Extended Reach Locking Tool Lanyard
48-22-8850	35 lbs	35 lbs Locking Tool Lanyard

Tether Tools When Working at Height

QUICK-CONNECT LOCKING TOOL LANYARD SYSTEM

BEST SHOCK
ABSORPTION

ANSI/ISEA
121-18

Integrated Swivel

Color Coded
Easy weight identification

Individualized Serial Numbers
Inventory management

Double-Locking Carabiner

Part #	Weight Rating	Description
48-22-8820	10 lbs	10 lbs Quick-Connect Locking Tool Lanyard
48-22-8822	5 lbs	3 Pc 5 lbs Quick-Connect Lanyard Accessory
48-22-8823	10 lbs	3 Pc 10 lbs Quick-Connect Lanyard Accessory

Quick Tool Change Out