


















SEWER & DRAIN MAINTENANCE

MACHINES	RECOMMENDED APPLICATION SELECTION			CABLE CAPACITY	
	APPLICATIONS	PIPE SIZES	MAX DISTANCE	CABLE SIZES	PIPE SIZES
 <p>MX FUEL™ Sewer Drum Machine w/ POWERTREDZ™</p>	 <p>Sewer Lateral Lines</p>	3" – 8"	200'	5/8" 3/4"	3" – 6" 4" – 8"
 <p>MX FUEL™ Sewer Drum Machine</p>	 <p>Sewer Lateral Lines</p>	3" – 8"	200'	5/8" 3/4"	3" – 6" 4" – 8"
 <p>M18 FUEL™ Sectional Machine</p>	 <p>Sinks Kitchen Sinks</p>  <p>Bathtubs Showers</p>  <p>Roofstacks</p>  <p>Sewer Lateral Lines</p>	1-1/4" – 6"	150'	5/8" 7/8"	1-1/4" – 2" 2" – 6"
 <p>M18 FUEL™ Sewer Sectional Machine w/ CABLE DRIVE™</p>	 <p>Sewer Lateral Lines</p>	2" – 8"	200'	7/8" 1-1/4"	2" – 6" 3" – 8"

MACHINES	RECOMMENDED APPLICATION SELECTION				
	APPLICATIONS	PIPE SIZES	MAX DISTANCE	CAMERA HEAD DIAMETER	PUSH CABLE DIAMETER
 <p>M18™ 120' Pipeline Inspection System</p>	 <p>Sewer Lateral Lines</p>	2" – 6"	120'	25mm	10mm
 <p>M18™ 200' Pipeline Inspection System</p>	 <p>Sewer Lateral Lines</p>	3" – 10"	200'	34mm	12mm

SEWER & DRAIN MAINTENANCE

DRUM MACHINE & DRUM CABLES	MILWAUKEE® PART #				DESCRIPTION	RIDGID® PART #	GENERAL® PART #	SPARTAN® PART #
	MXF500-1CP				MX FUEL™ Sewer Drum Machine Kit	K-6200 K-750 K-7500	P-MX P-SXL	300
								1065
	MXF501-1CP							2001
	48-53-2325				5/8" x 25' Inner Core Drum Cable	C-25	25EM4	03441702
	48-53-2350				5/8" x 50' Inner Core Drum Cable	C-26	50EM4	03441703
	48-53-2310				5/8" x 100' Inner Core Drum Cable	C-24	100EM4	03441705
	48-53-2425				3/4" x 25' Inner Core Drum Cable	C-28	25EM5	03442101
	48-53-2450				3/4" x 50' Inner Core Drum Cable	C-29	50EM5	03442102
	48-53-2410				3/4" x 100' Inner Core Drum Cable	C-100	100EM5	03442105
48-53-2802				5/8" x 2' Leader Cable	92555	LE-2	03441608	
48-53-2902				3/4" x 2' Leader Cable	92560	LE-3	04214010	
SECTIONAL MACHINE & SECTIONAL CABLES	MILWAUKEE® PART #				DESCRIPTION	RIDGID® PART #	GENERAL® PART #	
	2818-21				M18 FUEL™ Sectional Machine for 5/8" & 7/8" Cables	K-60SP	RT-66-C	
	2818B-21				M18 FUEL™ Sectional Machine with 5/8" Cable	K-60SP + A-35	I-95-A, RT-66-A	
	2818A-21				M18 FUEL™ Sectional Machine with 7/8" Cable	K-60SP-SE	I-95-C	
	2871-22				M18 FUEL™ Sewer Sectional Machine Kit w/ CABLE DRIVE™ (Accessories & Cables Sold Separately)	K-1500 K-5208	N/A	
	2871A-21							
	48-53-2680				5/8" x 7-1/2' All-Purpose Open Wind Sectional Cable	C-8	7.5R-8	
	48-53-2852				7/8" x 15' All-Purpose Open Wind Sectional Cable	C-12	15R-14	
	48-53-2851				1-1/4" x 15' All-Purpose Open Wind Sectional Cable	C-10	15R-10	
48-53-2854				1-1/4" x 15' Heavy Duty Open Wind Sectional Cable	C-11	15R-11		
ACCESSORIES	MILWAUKEE® PART #				DESCRIPTION	RIDGID® PART #	GENERAL® PART #	SPARTAN® PART #
	Drum	Sectional						
	All	5/8"	7/8"	1-1/4"				
		48-53-3812			Drop Head Straight Auger	N/A	N/A	N/A
		48-53-3811			Drop Head Bulb Auger	T-217	N/A	N/A
			48-53-3829		Flexible Straight Auger	T-101	R-HA-10	N/A
	48-53-2830		48-53-3830	48-53-4830	Straight Auger	T-1, T-2, T-5, T-101	G-HA, R-HA-10	N/A
			48-53-3828		Flexible Funnel Auger	T-102	R-RTR-10	N/A
		48-53-3813			Funnel Auger	T-206	N/A	N/A
	48-53-2831		48-53-3831	48-53-4831	Funnel Auger	T-3, T-4, T-102	RTR-2, G-RTR-2, R-RTR-10	N/A
			48-53-3825		2" Root Cutter	T-109	R-2UC-10/R-3UC-10	N/A
	48-53-2832		48-53-3832	48-53-4832	3" Root Cutter	T-413, T-408, T-50-1, T-150-1, T-111	3UC, 3HDSC, 3SCB, G-3HDSC, R-3UC-10	44161300, 02786600
	48-53-2833		48-53-3833	48-53-4833	4" Root Cutter	T-414, T-408, T-50-2, T-21, T-150-2	3UC, 4HDSC, 4CB, G-4HDSC	02790900, 44165200
	48-53-2834		48-53-3834	48-53-4834	6" Root Cutter	T-22, T-416	N/A	2813500
		48-53-3814			1-1/4" Opening Tool	T-210	R-AH	N/A
		48-53-3815			1-1/2" Opening Tool	T-211	N/A	N/A
		48-53-3827			2" Opening Tool	T-107	R-SHD-10	N/A
	48-53-2835		48-53-3835	48-53-4835	3" Opening Tool	T-406, T-107, T-112, T-113, T-24, T-25	SHD, G-SHD, R-SHD-10	2798800
	48-53-2836		48-53-3836	48-53-4836	4" Opening Tool	T-26, T-26A	N/A	N/A
48-53-2837		48-53-3837	48-53-4837	3" Grease Cutter	T-31, T-114	N/A	3416600	
48-53-2838		48-53-3838	48-53-4838	4" Grease Cutter	T-32	N/A	3416700	
INSPECTION	MILWAUKEE® PART #				DESCRIPTION	RIDGID® PART #	GENERAL® PART #	SPARTAN® PART #
	2974-22				M18™ 200' Pipeline Inspection System Kit	RIDGID® SeeSnake® HDR TruSense Self-Leveling Color Camera Reel 63603	Gen-Eye Self Leveling Color Camera with 200' Gel-Rod (SL-SDP-A)	Explorer L200 Video Inspection System (6405L200)
2973-22				M18™ 120' Pipeline Inspection System Kit	Compact C40 63668 and Compact M40 63673	Gen-Eye C-M-SDW-A with 100' Mini Color Camera Gel-Rod	N/A	