

CABLE AND ACCESSORY MATRIX

	LINE SIZE	CABLE DIAMETER	MODEL #	DESCRIPTION	COMPATIBLE WITH	HEAD ATTACHMENTS w/ RUST GUARD™ PLATING				
AUGER CABLES	1-1/4" – 2"	3/8"	48-53-2577	3/8" x 6' Bulb Head TRAPSSNAKE™ Urinal	TRAPSSNAKE™ 4' Urinal Auger 3574, 49-16-3574	N/A				
	2" – 4"	1/2"	48-53-2576	1/2" x 4' Bulb Head TRAPSSNAKE™ Toilet	TRAPSSNAKE™ 6' Toilet Auger 3576, 49-16-3576	N/A				
	1/2" – 2"	1/4"	48-53-2578	1/4" x 25' Drop Head Cable	TRAPSSNAKE™ 25' Auger w/ CABLE DRIVE™ 49-16-2573	N/A				
	1/2" – 2"	1/4"	48-53-2579	1/4" x 25' Bulb Head Cable	TRAPSSNAKE™ 25' Auger w/ CABLE DRIVE™ 49-16-2573	N/A				
HANDHELD MACHINE CABLES	1-1/4" – 2"	1/4"	48-53-2563	1/4" x 25' Inner Core Bulb Head w/ RUST GUARD™	M12™ Drain Snake – 2571 M18 FUEL™ Drain Snake w/ CABLE DRIVE™ – 2772	N/A				
			48-53-2564	1/4" x 25' Inner Core Drop Head w/ RUST GUARD™						
			48-53-2671	1/4" x 35' Inner Core Bulb Head w/ RUST GUARD™	M18 FUEL™ Drain Snake w/ CABLE DRIVE™ 2772					
			48-53-2672	1/4" x 50' Inner Core Bulb Head w/ RUST GUARD™						
	1-1/4" – 2-1/2"	5/16"	48-53-2561	5/16" x 25' Inner Core Bulb Head w/ RUST GUARD™	M12™ Drain Snake – 2571 M18 FUEL™ Drain Snake w/ CABLE DRIVE™ – 2772	N/A				
			48-53-2562	5/16" x 25' Inner Core Drop Head w/ RUST GUARD™						
			48-53-2673	5/16" x 35' Inner Core Bulb Head w/ RUST GUARD™	M18 FUEL™ Drain Snake w/ CABLE DRIVE™ – 2772					
			48-53-2674	5/16" x 50' Inner Core Bulb Head w/ RUST GUARD™						
2" – 3"	3/8"	48-53-2676	3/8" x 25' Inner Core w/ RUST GUARD™	M18 FUEL™ Drain Snake w/ CABLE DRIVE™ 2772	48-53-2685	2" – 3" Head Attachment Kit	48-53-2681	Small Bulb Head		
		48-53-2675	3/8" x 35' Inner Core w/ RUST GUARD™				48-53-2682	Small Drop Head		
							48-53-2683	1" Spade Bit		
							48-53-2684	1" C-Cutter		
DRUM MACHINE CABLES	1-1/4" – 2"	5/16"	48-53-2772	5/16" x 75' Inner Core Drop Head w/ RUST GUARD™	M18 FUEL™ SWITCH PACK™ Sectional Drum Machine 2775	N/A				
	1-1/4" – 3"	5/8"	48-53-2775	5/8" x 50' Flexible Open Wind w/ RUST GUARD™	M18 FUEL™ SWITCH PACK™ Sectional Drum Machine 2775	48-53-2685	2" – 3" Head Attachment Kit	48-53-2681	Small Bulb Head	
								48-53-2682	Small Drop Head	
								48-53-2683	1" Spade Bit	
								48-53-2684	1" C-Cutter	
	1-1/2" – 3"	3/8"	48-53-2776	3/8" x 75' Inner Core Cable	M18™ Drum Machine 2817	48-53-2790	3" – 4" Head Attachment Kit	48-53-2786	Medium Funnel Head	
	1-1/2" – 3"	3/8"	48-53-2777	3/8" x 100' Inner Core Cable						48-53-2787
										48-53-2788
								48-53-2789	1-1/2" C-Cutter	
	2" – 3"	3/8"	48-53-2773	3/8" x 50' Inner Core w/ RUST GUARD™	M18 FUEL™ SWITCH PACK™ Sectional Drum Machine 2775	48-53-2790	3" – 4" Head Attachment Kit	48-53-2786	Medium Funnel Head	
										48-53-2787
								48-53-2788	1-1/2" Spade Bit	
								48-53-2789	1-1/2" C-Cutter	
3" – 4"	1/2"	48-53-2774	1/2" x 25' Inner Core w/ RUST GUARD™	M18 FUEL™ SWITCH PACK™ Sectional Drum Machine 2775	48-53-2790	3" – 4" Head Attachment Kit	48-53-2786	Medium Funnel Head		
							48-53-2788	1-1/2" Spade Bit		
							48-53-2789	1-1/2" C-Cutter		
3" – 4"	1/2"	48-53-2778	1/2" x 75' Inner Core Cable	M18™ Drum Machine 2817	48-53-2790	3" – 4" Head Attachment Kit	48-53-2786	Medium Funnel Head		
							48-53-2788	1-1/2" Spade Bit		
							48-53-2789	1-1/2" C-Cutter		