

M12**2" COPPER TUBING CUTTER**

M12 CTC2

Voltage	M12
Motor Type	Brushless
Tool Dimensions (mm)	321.8 x 97.8 x 139.7
Material Application	Copper Pipe
Pipe capacity (mm)	34.92, 41.28, 53.98 (Outer Diameter)
Cut Clearance (mm)	53
Auto-Adjust to Pipe Size	Yes
LED Light	Yes
View Window	Yes
Tool Weight (Bare Tool) (kg)	2.7

**ACCESSORIES**

48-38-4257	Replacement Wheel for M12 2" Copper Tubing Cutter (2 PK)
------------	--

**M18****M18 FUEL 5CFM VACUUM PUMP**

M18 FVP5

Voltage	18V
Flow Rate	5 CFM (142 L/min)
Ultimate Vacuum	25 Microns
Port Compatibility	1/4", 3/8", 1/2" & 5/16" Adaptor
Pump Type	Two-Stage Rotary Vane
Oil Capacity	550 ml
Manifold Mode	Yes
Gas Ballast Valve	Yes
Isolating Ball Valve	Yes
Internal Check Valve	Yes
Weight w/ 8.0Ah Battery Pack (kg)	9.6

**M18 FUEL 1 1/4" COMPACT PIPE THREADER WITH 1/2"-1 1/4" COMPACT BSPT HIGH SPEED DIE HEADS**

M18 FPT114

Voltage	18V
Rated Speed	0 – 35/min
MILWAUKEE Die Head Range	1/2", 3/4", 1" & 1 1/4"
Die Thread Type	NPT / BSPT
Die Type	Alloy / High Speed
AUTOSTOP	Yes
Variable Speed	Yes
Weight w/ 8.0Ah Battery Pack (kg)	5.8

**ACCESSORIES****PIPE THREADER DIES**

4932480227	BSPT Alloy Die 1/2"	48-36-1101	NPT Alloy Die 1/2"
4932480228	BSPT Alloy Die 3/4"	48-36-1102	NPT Alloy Die 3/4"
4932480229	BSPT Alloy Die 1"	48-36-1103	NPT Alloy Die 1"
4932480230	BSPT Alloy Die 1-1/4"	48-36-1104	NPT Alloy Die 1-1/4"
4932480233	BSPT HS Die 1/2"	48-36-1107	NPT HS Die 1/2"
4932480234	BSPT HS Die 3/4"	48-36-1108	NPT HS Die 3/4"
4932480235	BSPT HS Die 1"	48-36-1109	NPT HS Die 1"
4932480236	BSPT HS Die 1-1/4"	48-36-1110	NPT HS Die 1-1/4"

PIPE THREADER DIE HEADS

4932480245	BSPT Alloy Die Head 1/2"	48-36-1307	NPT Alloy Die Head 1/2"
4932480246	BSPT Alloy Die Head 3/4"	48-36-1308	NPT Alloy Die Head 3/4"
4932480247	BSPT Alloy Die Head 1"	48-36-1309	NPT Alloy Die Head 1"
4932480248	BSPT Alloy Die Head 1-1/4"	48-36-1310	NPT Alloy Die Head 1-1/4"

M18 FORCE LOGIC 2"-3" PEX EXPANSION TOOL

M18 ONEBLPXPL

Voltage	18V
Head Type	Auto-Rotating
Stroke Length (mm)	55.5
Weight w/ 5.0Ah Battery Pack (kg)	10.1

**M18 TRANSFER PUMP**

M18 BTP

Voltage	18V
Flow Rate (l/m)	30
IP Protection Class	IPX4
Max. Head Height (m)	23
Max Suction Height (m)	5.5
Max Water Temperature (°C)	60
Thread Size (mm)	3/4"(19 mm) Male BSPT
Weight w/ 5.0Ah Battery Pack (kg)	4.1

