

Project Name

Location

Prepared By



## SATCO S11241

A19/6W/LED/RGBTW/CL

### Notes

(www) 07-02-2023 00:53:07

### General

|                         |                        |
|-------------------------|------------------------|
| Status                  | Active                 |
| Watts                   | 6W                     |
| Incandescent Equivalent | 40W                    |
| Volts                   | 120V                   |
| Shape                   | A19                    |
| Base                    | Medium                 |
| ANSI Base               | E26                    |
| Finish                  | Clear                  |
| CCT (Kelvin)            | 2700K-5000K            |
| Temperature             | RGB and Tunable White  |
| CRI                     | 90+                    |
| Lumens                  | 450L                   |
| Beam Spread             | 320                    |
| Dimmable                | Yes-Dimmable           |
| Dimming Note            | Only with Starfish App |
| Hours Rated             | 15000                  |
| Product Category        | Type A                 |
| Technology              | LED                    |

### Electrical

|                       |                            |
|-----------------------|----------------------------|
| Operating Frequency   | 60Hz                       |
| Power Factor          | 0.7                        |
| Operating Temperature | -20C (-4F) to +40C (+104F) |

### Physical

|               |      |
|---------------|------|
| MOL           | 4.33 |
| MOD           | 2.36 |
| Housing Color | None |
| Weight (lb.)  | 0.08 |

### Additional Information

|                            |         |
|----------------------------|---------|
| Rated For Enclosed Fixture | Yes     |
| Warranty                   | 2-Years |

### Compliance

|                            |                               |
|----------------------------|-------------------------------|
| Safety Listing             | cULus - Listed                |
| Location Rating            | Damp                          |
| California Status          | Lawful for sale in California |
| Title 20 / 24 Status       | Lawful for sale               |
| RoHS Compliant             | Yes                           |
| FCC Compliant              | Yes                           |
| Canadian Standard ICES-005 | Class B                       |
| SDS Sheet                  | LED_Lamp                      |