

Project Name

Location

Prepared By



SATCO S11670

24WLED/DW/DNL3/FS/RND/DD/WH

Notes

(www) 07-07-2023 00:13:04

General

Status	Active
Recessed Can Size	3 in.
Wattage	16W/20W/24W
Voltage	120V-277V
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm White to Natural Light
Lumen Output	1300L/1600L/2000L
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90+
Beam Angle	40
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	Dual Dimming: Phase-Cut and 0-10V
Sloped Ceiling	No

Dimensions

Width (in.)	5.2
Height (in.)	3.62
Weight (lb.)	2.17

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
ENERGY STAR	Yes
ES Unique ID	ESID-3999680
Air Tight Rated	Yes
IC Rated	Yes
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B
SDS Sheet	LED_Fixture

Additional Information

Specification Note	Default CCT setting: 2700K; Default wattage setting: 20W
Warranty	5-Years