

# PINNACLE 170

## **TL170-UL24V**

24V LED Specification Grade Tape Light

**SPECIFICATION SHEET** 





## **DESCRIPTION**

NDR Pinnacle 170 Series LED tape light offers industry leading specification grade technology and is designed specifically for longer runs up to a max run of 49.2ft on a single 96W LED driver. Being able to install longer runs with no visible lumen drops, reduces installation costs by reducing the amount of drivers needed and simplifying the installation process which saves you time.

To ensure a consistent color temperature and light output, all our LED chips are selected from 1 bin using the 3-Step MacAdam binning criteria and have an industry leading CRI97+ rendering index. Ideal applications: ambient and close level task lighting. Well-suited for longer applications such as hallways, toe kicks, coves, display cases and more.

## **FEATURES**

3-Step MacAdam LED binning 3oz. copper Cuttable every 4" Full range dimmability IP20 rated – Dry location

## **SPECIFICATIONS**

Model	TL170-UL24V
Certificates	cULus
Input voltage	24V
Watts/FT	1.9W/FT
Lumens/FT	170 lm/FT
Watts/m	6.2W/m
Lumens/m	557 lm/m
CRI	97+
Dimmable	Yes
IP rating	IP20
Dimensions	0.4" x 590" x 0.07" (10mm x 15000mm x 1.8mm)
Cuttable section	Every 4" (100mm)
Beam angle	120°
Lifetime	50,000 hours
Mounting	3M self-adhesive tape (non-porous)
Operating temperature	-4°F to 113°F (-20°C to 45°C)
Max run	49.2ft (15m)
Limited warranty	5 years



# STOCKING SKUs

Model	Watts/FT	lm/FT	Watts/m	lm/m	CRI	Reel size	IP Rating	Lifetime	Ltd. Warr.
TL170-UL24-27K	1.9	170	6.2	557	97+	49.2FT (15m)	IP20	50,000h	5 years
TL170-UL24-3K	1.9	170	6.2	557	97+	49.2FT (15m)	IP20	50,000h	5 years
TL170-UL24-4K	1.9	170	6.2	557	97+	49.2FT (15m)	IP20	50,000h	5 years
TL170-UL24-5K	1.9	170	6.2	557	97+	49.2FT (15m)	IP20	50,000h	5 years

## **RATINGS & CERTIFICATIONS**









## ACCESSORIES



**TL-STT-2-10**2-Pin screw connector, tape to tape connector (8-10mm)



**TL-STB-2-10**2-Pin screw connector terminal block (8-10mm)



**TL-DUAL-2-10**2-Pin screw connector, tape-to-tape & tape-to-wire lead terminal block dual connector



**TL-SLTT-2-10**2-Pin screw connector, tape to tape L-corner (8-10mm)



**TL-STW8-2-10**2-Pin screw connector, tape to 8" wire lead (8-10mm)



## ACCESSORIES (continued)



## **TL-SJOIN8-2-10**

2-Pin screw connector, tape to tape with 8" wire lead (8-10mm)



#### TL-EXT6FT-2-10

2-Pin Screw Connector - 6 Foot Extension (8-10mm)

## DRIVERS



## **TLD24V-30W**

30W Class 2 LED driver 100-277V input, 24V output TRIAC, ELV, MLV, Forward & reverse phase, PWM output 1/2" knockout size Wet locations rated Dimensions: 6.5" x 3.7" x 1.6" (165mm x 94.5mm x 40mm)



## **TLD24V-60W**

60W Class 2 LED driver

100-277V input, 24V output TRIAC, ELV, MLV, Forward & reverse phase, PWM output 1/2" knockout size Wet locations rated Dimensions: 7.4" x 3.7" x 1.6" (188mm x 94.5mm x 40mm)



## **TLD24V-96W**

96W Class 2 LED driver 100-277V input, 24V output TRIAC, ELV, MLV, Forward & reverse phase, PWM output 1/2" knockout size Wet locations rated Dimensions: 8.7" x 3.7" x 1.6" (220mm x 94.5mm x 40mm)



## TLD24V-192W

192W Class 2 LED driver 100-277V input, 24V output x2 (2x 96W output) TRIAC, ELV, MLV, Forward & reverse phase, PWM output 1/2" knockout size Wet locations rated Dimensions: 10.9" x 4.3" x 1.8" (278mm x 110mm x 40mm)



## DRIVERS (continued)



#### TLD24V-288W

288W Class 2 LED driver 100-277V input, 24V output x3 (3x 96W output) TRIAC, ELV, MLV, Forward & reverse phase, PWM output 1/2" knockout size Wet locations rated Dimensions: 11.9" x 4.3" x 1.8" (301mm x 110mm x 45mm)



## **TLD24V-25W**

25W LED driver for Pinnacle Series Puck Light and Tape Light 120V input, 24V output Dry location rated Dimensions: 6.1" x 2.1" x 0.8" / 155mm x 54mm x 20mm



## TLD24V-MINI-60W

60W Class 2 LED transformer 120V input, 24V output, ELV dimming ONLY Requires junction box for UL rated Dimensions: 3.3" x 1.6" x 1" / 84mm x 40mm x 25mm



## TLDDIM24V-100W

100W LED dimmer and 24V driver 120V input, 24V output Dry location rated Dimensions: 2.1" x 4.1" x 1.4" / 54mm x 105mm x 35mm