








**HOFFMAN**





















CMFK  
CMFKSS  
CMTGFT  
GMTBKTMS


  → 



  → 





A-A









 

CMFK  
CMFKSS  
CMTGFT  
GMTBKTMS



B-B



→

CMFK  
CMFKSS  
CMTGFT  
GMTBKTMS

→

1

(4X)


(6X)


- 6 -

© 2018 Hoffman Enclosures Inc.




PH 763 422 2211 • nVent.com/HOFFMAN



89083877





CMFK  
CMFKSS  
CMTGFT  
GMTBKTMS

  → 

  → 