

Mini circuit breaker, Homeline Canadian, 35A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

CHOM235

## Main

Range of product	Homeline	
Product or component type	Miniature circuit-breaker	
[In] rated current	35 A	
[Ue] rated operational voltage	120/240 V AC	
Mounting mode	Plug-on	
Poles description	2P	
Short-circuit current	10 kA	
Circuit breaker type	Standard	
Circuit breaker application	HACR rated	
Electrical connection	Screw clamp terminals	

# Complementary

Number of spaces required	2
AWG gauge	AWG 8AWG 2 aluminum/copper

### **Environment**

Product certifications	CSA
Ambient air temperature for operation	104 °F (40 °C)

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	2.50 in (6.35 cm)
Package 1 Weight	11.840 oz (335.658 g)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

## **Technical Illustration**

### **Dimensions**

