



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 200A  
3P 600V NO FUSE HD TYPE 4XW/WINDOW

principle of operation of the actuating element	SINGLE THROW
mechanical service life (switching cycles) typical	8000
fastening method	2 OR 3 POINT MOUNTING HOLES
number of poles	3
ampacity	200 A
supply voltage frequency rated value 50/60 Hz	Yes
voltage between phase and Ground (GND) rated value	600 V
product brand name	SIEMENS
product type designation	ENCLOSED/SAFETY SWITCH
design of the housing	TYPE 4X
material	304SS
certificate of suitability	UL

last modified:

1/6/2021 