



PRODUCT-DETAILS

DO524

Digital output module. 32 DO: 24VDC 0.5A
(DO524)



General Information	
Extended Product Type	DO524
Product ID	1SAP240700R0001
ABB Type Designation	DO524
EAN	4013614482717
Catalog Description	Digital output module. 32 DO: 24VDC 0.5A (DO524)
Long Description	DO524: S500 Digital output module. 32 DO: 24VDC 0.5A. 1-wire.

Ordering	
CN8	85389091
Invoice Description	Digital output module. 32 DO: 24VDC 0.5A (DO524)
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0.106 kg
Product Net Depth / Length	62 mm
Product Net Height	76 mm
Product Net Width	67.5 mm
Gross Weight	0.13 kg
Package Level 1 Depth / Length	84 mm
Package Level 1 Height	72 mm
Package Level 1 Width	71 mm
Package Level 1 Units	1 carton

Certificates and Declarations

Declaration of Conformity - CE	3ADR980146
REACH Date	20241206
REACH Declaration	3ADR980139
REACH Information	True - contains substances > 0.1 mass percentage
SCIP	16b29f4e-e363-43ca-ad6f-2d21b7f75cfa Germany
RoHS Date	2013
RoHS Declaration	3ADR980146
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Technical

Function	32 DO: 24VDC 0.5A
Number of Digital Outputs	32
Number of Digital Configurable I/Os	0
Output	Transistor
Output Voltage Type	DC
Output Current	0.5 A
Output Voltage Maximum	20.4 ... 28.8 V
Degree of Protection	IP20
Supply Voltage	20.4 ... 28.8 V DC

Additional Information

Product Main Type	DO524
Product Name	Distributed Automation I/Os

External Classifications and Standards

eClass	27-24-22-04
ETIM 8	EC001419 - PLC digital I/O-module
ETIM 9	EC001419 - PLC digital I/O-module
ETIM 10	EC001419 - PLC digital I/O-module
UNSPSC	32151705

Environmental	
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
PLC Automation → Programmable Logic Controllers PLCs → AC500 → S500 I/O modules

