

	Catalogue Number	Alternate Cat. No.	Size or Description		Packaging Case Box	
Jack Chain - Steel - Bright Zinc Plated			Skid Qty			
	JC10-50		T10	43lbs.	300	50
	JC10-100		T10	43lbs.	600	100
	JC10-250R		T10	43lbs. 40 x rls	250' reel	
	JC10-250B		T10	43lbs. 40 x bkts	250' bucket	
	JC12-50		T12	29lbs	300	50
	JC12-300R		T12	29lbs 40 x rls	300' reel	
	JC12-300B		T12	29lbs 40 x bkts	300' bucket	
	JC14-100		T14	16lbs.	1000	100
	LC2-100		#2	115lbs.	600	100
	LC3-100		#3	90lbs.	600	100
	LC3-300R		#3	90lbs. 40 x rls	300' reel	
	LC3-300B		#3	90lbs. 40 x bkts	300' bucket	
	LC4-100		#4	70lbs.	600	100
	LC4-250B		#4	70lbs. 40 x bkts	250' bucket	
	B = Bucket R = Reel					
STAINLESS STEEL - #10 Jack Chain						
	JC10-100-SS	Type 304 SS	#10	43lbs.		100
*** Please note: 40 Buckets of Jack Chain on a skid. Custom labeling available on orders of 20 Buckets or More. ***						
Fluorescent Light Fixture Hanger Hooks						
	11430		Top/End Mount 4.125" x 2.375", Wire Dia @ 0.135"		-	100
Fixture Hooks						
	M12		M12 Screw Hook, 3" Length, Zinc Plated		-	100
S-Hooks						
	S10		T10		1000	100
Tie Wire (Steel - 16 Gauge)						
	TW-16		300' / coil		-	16
Perforated Strapping						
	962		3/4" x 10'		-	50
Poly Twine & Yellow Polypro Rope						
	PTW-1/4	max pull strength 1120 lbs.	1/4"		Reel Length 1,300'	
	PTW-3/16	625	3/16"		2,125	
	PTW-5/16	1450 lbs.	5/16"		975'	
	PTW-3/8	2250 lbs.	3/8"		630'	
	PTW-1/2	4200 lbs.	1/2"		335'	
	PTW-5/8	6495 lbs.	5/8"		200	
	PTW-3/4	8310 lbs.	3/4"		125	
	PTW-1	17,710 lbs.	1"		600	
	PL-210	210 lbs.	Poly-Tying Twine		6,500' / Pail	
	PL-210B		210 Poly-Tying Twine		6,500'/BOX	