

Product data sheet

Specifications



Mini circuit breaker, Homeline
Canadian, 15A, 2 pole,
120/240VAC, combo arc fault, plug
in

CHOM215CAFI

Main

Range of product	Homeline
Product or component type	Miniature circuit-breaker
[In] rated current	15 A
Connections - terminals	Pigtail neutral
[Ue] rated operational voltage	120/240 V AC
Poles description	2P
Short-circuit current	10 kA
Circuit breaker type	Combination ARC-fault
Electrical connection	Pigtail connector

Complementary

Number of spaces required	2
---------------------------	---

Environment

Product certifications	CSA
Ambient air temperature for operation	104 °F (40 °C)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.800 in (9.652 cm)
Package 1 Width	6.00 in (15.24 cm)
Package 1 Length	2.50 in (6.35 cm)
Package 1 Weight	17.920 oz (508.024 g)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
Halogen content performance	Halogen free product

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No