

# Waterproof Power Box

P55/P54/P45-D01



## Key Features

- Aluminum Alloy and SECC Construction
- Max. Load Capacity: 17.6 lb (8.0 kg)
- Compatible With Wall, Corner, and Pole Mounts
- IP66 Rating

## Learn More



View the accessory selector for all mount options.

## Specifications

Weight	3.4 kg (7.5 lb)
Load Bearing Capacity	8.0 kg (17.6 lb)
Material	Aluminum Alloy and SECC
Color	White
Dimensions	Φ60.8mm x 49.0mm (Φ2.4 in. x 1.9 in.)
Thread Size	G½ in.
IP Rating	IP66
Operating Temperature	−40 °C to 60 °C (−40 °F to +140 °F) < 90% (RH)
Storage Temperature	−40 °C to 60 °C (−40 °F to +140 °F) 10% to 90% (RH)