

Pole Mount Bracket

P01



Key Features

- SECC and SUS304 Construction
- Max. Load Capacity: 22.1 lb (10.0 kg)

Learn More



View the accessory selector for all mount options.

Specifications

Weight	1.1 kg (2.4 lb)
Load Bearing Capacity	10.0 kg (22.1 lb)
Material	SECC and SUS304
Color	White
Mast Diameter	Φ 80.0 mm to 150.0 mm (Φ 3.2 in. to 5.9 in.)
Dimensions	130.4 mm x 170.0 mm x 45.0 mm (5.1 in. x 6.7 in. x 1.8 in.)