

Project Name

Location

Prepared By



SATCO S11100

A19/10W/LED/RGBTW/SF

Notes

(www) 18-13-2023 09:07:05

General

Status	Active
Watts	10W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	RGB and Tunable White
CRI	90+
Lumens	800L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	25000
Technology	LED

Smart Product Info

IOT Enabled	Yes
Operational Humidity	10% - 85% R.H.
Number of Switching Cycles	100000
Software Upgradeable	Yes
Communication Protocol	WiFi-2.4GHz
Voice Assistants Supported	Alexa; Google Home; Siri; SmartThings
Software Supported	Tuya/Starfish APP

Electrical

Operating Frequency	60Hz
---------------------	------

Specifications

Dimming Type	Smart-Starfish App only
Dimming Note	Only with Starfish App
Power Factor	>0.9
Operating Temperature	-25C (-13F) to +40C (+104F)

Physical

MOL	4.25
MOD	2.36
Housing Color	White
Lens Finish	Mirrored
Lens Material	Polycarbonate (PC)
Weight (lb.)	0.09

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3-Years

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp