



Catalog No. SH4624L12-6

Description: HDG TRAY 6IN 24W LAD STR. 6M

UPC No 785055247920

Home > Wire & Cable Management > T&B Cable Tray > Channel Cable Tray Straight Sections

Series 4 steel hot-dipped galvanized after fabrication straight section 6 inches side rail height 24 inches width ladder 12 inches rung spacing 6 meters length

Representative Image

Descriptors

Category	Channel Cable Tray Straight Sections
Application	Schools, hospitals, office buildings, airports, casinos, stadiums, petrochemical plants, automotive plants paper plants, food processing, power plants refineries, manufacturing, mining.

Specifications

Material	Steel
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	T&B Cable Tray
Standard	CSA, NEMA, NEC, UL CSA, NEMA, NEC, UL

Dimensions

Width	24 in
Length	6 m
Side Rail Height	6 inches

ETIM	EC000854 Cable ladder/wide span cable ladder
Type of rung	Perforated profile
Fixation rung	Welded
Height	152.4 mm
Width	609.6 mm
Length	6000 mm
Material	Steel
Surface protection	Hot-dip galvanized

