





---

 PRODUCT-DETAILS

## PS1-4-1-65

PS1-4-1-65 3-phase busbar for 4 MS116 / MS132 with 1 HK/SK, I<sub>e</sub>=65A




---

### General Information

Extended Product Type	PS1-4-1-65
Product ID	1SAM201906R1114
EAN	4013614400742
Catalog Description	PS1-4-1-65 3-phase busbar for 4 MS116 / MS132 with 1 HK/SK, I <sub>e</sub> =65A
Long Description	PS1-4-1-65 3-phase busbars ensure a quick and safe connection of 4 MS132 or MS116 manual motor starters with 1 lateral auxiliary contacts and are therefore a cost effective solution. The rated current is 65 A.

---

### Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85369010

---

### Popular Downloads

Data Sheet, Technical Information	1SBC100214C0202
Instructions and	2CDC131011M6802

Manuals	2CDC131034M6801 2CDC131022M6802
Instructions and Manuals (Part 3)	1SBC100214C0202
CAD Dimensional Drawing	2CDC001079B0201
Dimension Diagram	1SAM200450F0007

## Dimensions

Product Net Width	203.5 mm
Product Net Height	32.3 mm
Product Net Depth / Length	13 mm
Product Net Weight	0.087 kg

## Technical

Rated Operational Voltage	690 V AC 250 V DC
Rated Operational Current (I <sub>e</sub> )	65 A
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	6 kV
Degree of Protection	IP20
Pollution Degree	3
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
-------------------------------------	-----------------------

## Environmental

Ambient Air Temperature	Operation -25 ... +70 °C Storage -50 ... +80 °C
----------------------------	--

## Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SAA963005-4502
RoHS Declaration	No declaration needed
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006539
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Certificates and Declarations

---

cUL Certificate	1SAA963001-1701
Declaration of Conformity - CE	1SAD101100-3411
Declaration of Conformity - UKCA	1SAD201100-3411
UL Certificate	E121190-20000619

---



---

## Container Information

---

Package Level 1 Units	box 10 piece
Package Level 1 Width	80 mm
Package Level 1 Depth / Length	264 mm
Package Level 1 Height	46 mm
Package Level 1 Gross Weight	0.92 kg
Package Level 1 EAN	4013614488122

---



---

## External Classifications and Standards

---

Object Classification Code	W
ETIM 9	EC000215 - Phase busbar
ETIM 10	EC000215 - Phase busbar
eClass	V11.0 : 27371306
UNSPSC	39121117
IDEA Granular Category Code (IGCC)	4378 >> Phase busbar
E-Number (Finland)	3705924
E-Number (Norway)	4364006
E-Number (Sweden)	3111681

---



---

## Categories

---

Low Voltage Products and Systems → Circuit Breakers → Manual Motor Starters

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters

