



Project / Job Name:

Location:

Fixture Type:

Notes:

65-925 - Starfish; SMART Outdoor Pan & Tilt Camera; White Finish



GENERAL

Company	NUVO
EA Height	4.41
EA Width	3.74
EA Length	6.54
Bulb Included	Integrated
Camera Resolution	3MP(2304x1296), 640 x 480(VGA)
Starfish Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Diameter	3.09
Extends (in)	3.75
Material	Plastic
Fixture Type	Security Camera
Camera Focal Length	3.6
Camera Image Compression	H.264
Camera Image Sensor	CMOS
Includes	Mounting Hardware and Accessories; USB A Cord; Plug Adapter; 32GB SD Card
Status	Active
Camera Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card
Camera Viewing Angle	110 D; 96 H
Starfish Voice Assistants Supported	Alexa, Google Home, Siri, SmartThings
Camera WDR	Digital Wide Dynamic
CCT Selectable	False
Wattage Selectable	False
Finish Family	White
Additional Info	Video stream supported on Alexa Show devices
Amps	1.000A
Camera Audio	2-Way Communication
Camera Audio Compression	PCM
Has Camera	True
IOT Enabled	True
Starfish Operational Humidity	20% to 95% non-condensing
Starfish Software Supported	AWS Cloud Security Servers, Tuya/Starfish App
Indoor Outdoor	Outdoor
Product Technology	Not Applicable

ELECTRICAL

CCT (Kelvin Temp)	6000K
Dimmable	Non-Dimmable
Color Temp	Daylight
CRI	80+
Operating Temp	-10C (+14F) to +50C (+122F)
Lumens	400L
Volts	12V
Watts	2W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED

ADDITIONAL INFO

Warranty	1-Year
----------	--------

FEATURES

Camera Night Vision	4 pcs; LED; IR Distance 10m
---------------------	-----------------------------

PACKAGING

UPC	045923664564
Case Cube	1.5152
Case Height	9.65
Case Length	19.69
Case Quantity	20
Case UPC	10045923664561
Case Weight	49.6
Case Width	13.78
EA Cube	0.0624
EA Height	4.41
EA Length	6.54
EA Quantity	1
EA Weight	0.65
EA Width	3.74
Inner Cube	0.0
Pack Type	Box
Web Height	4.43
Web Width	3.09

COMPLIANCE

ADA Compliant	True
CA Regulations	T20 Exempt - Fixtures Not Regulated
CA Prop 65	Lead
CA Status	Lawful for sale in California
FCC Compliant	True
IP Rating	IP65
Location Rating	Wet
Safety Listing	cETLus
CA Compliance Text	Lawful for sale
Title 20	Exempt
T24 Compliant	False