



Project / Job Name:

Location:

Fixture Type:

Notes:

65-945R1 - Starfish; SMART Indoor Pan & Tilt Camera; White Finish



GENERAL

Company	NUVO
EA Height	7.09
EA Width	3.07
EA Length	3.19
Camera Resolution	3MP(2304x1296)
Starfish Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Extends (in)	2.8
Material	Plastic
Fixture Type	Security Camera
Camera Focal Length	4.0
Camera Image Compression	H.265/H.264
Camera Image Sensor	1/3 Color CMOS
Includes	Mounting Hardware and Accessories; USB C Cord; Plug Adapter
Product Notes	Pan & Tilt 0 to 355 Degrees & -10 to 40 Degrees
Status	Active
Camera Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card
Camera Viewing Angle	102 D; 81 H; 43 V; FOV 102 Degrees
Starfish Voice Assistants Supported	Alexa, Google Home, Siri, SmartThings
Wattage Selectable	False
Finish Family	White
Additional Info	Video stream supported on Alexa Show devices
Camera Audio	2-Way Communication
Has Camera	True
IOT Enabled	True
Starfish Operational Humidity	0% - 93%
Starfish Software Supported	AWS Cloud Security Servers, Tuya/Starfish App
Indoor Outdoor	Indoor
Product Technology	Not Applicable

ELECTRICAL

Operating Temp	-10C (+14F) to +45C (+113F)
Volts	5V

PHYSICAL

Finish	WHITE
--------	-------

ADDITIONAL INFO

Warranty	1-Year
----------	--------

FEATURES

Camera Night Vision	IR Distance 10m
---------------------	-----------------

PACKAGING

UPC	045923411588
Case Cube	0.9747
Case Height	15.16
Case Length	15.94
Case Quantity	20
Case UPC	10045923411585
Case Weight	15.1
Case Width	6.97
EA Cube	0.0402
EA Height	7.09
EA Length	3.19
EA Quantity	1
EA Weight	0.37
EA Width	3.07
Pack Type	Box
Web Height	4.33
Web Length	3.58
Web Width	2.52

COMPLIANCE

ADA Compliant	True
CA Regulations	T20 Exempt - Fixtures Not Regulated
CA Prop 65	Lead
CA Status	Lawful for sale in California
FCC Compliant	True
Safety Listing	Not Applicable
CA Compliance Text	Lawful for sale
Title 20	Exempt