



Project / Job Name:

Location:

Fixture Type:

Notes:

**65-935** - Starfish; SMART Doorbell Security Camera;  
White Doorbell with White Chime



#### GENERAL

Company	NUVO
EA Height	6.5
EA Width	2.6
EA Length	4.92
Camera Resolution	1080P
Starfish Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Extends (in)	1.19
Material	Plastic
Fixture Type	Security Camera
Camera Focal Length	2.8
Includes	Mounting Hardware and Accessories; USB A Cord; Plug Adapter; 32GB SD Card
Product Notes	Anti-disassembly alarm; White Doorbell with White Chime
Status	Active
Camera Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card
Starfish Voice Assistants Supported	Alexa, Google Home, Siri, SmartThings
Finish Family	White
Additional Info	5000mAh Rechargeable Battery; 4 to 6 Month Battery Life (based on 10 activations a day); Video stream supported on Alexa Show devices
Camera Audio	2-Way Communication
Has Camera	True
IOT Enabled	True
Starfish Operational Humidity	10% to 95% non-condensing
Starfish Software Supported	AWS Cloud Security Servers, Tuya/Starfish App
Indoor Outdoor	Outdoor
Product Technology	Not Applicable

#### ELECTRICAL

Operating Temp	-20C (-4F) to +45C (+113F)
Volts	5V

#### PHYSICAL

Finish	WHITE
--------	-------

#### ADDITIONAL INFO

Warranty	1-Year
----------	--------

#### FEATURES

Camera Night Vision	IR Distance 15 Feet
---------------------	---------------------

#### PACKAGING

UPC	045923664571
Case Cube	0.9056
Case Height	8.27
Case Length	17.17
Case Quantity	12
Case UPC	10045923664578
Case Weight	11.16
Case Width	11.02
EA Cube	0.0481
EA Height	6.5
EA Length	4.92
EA Quantity	1
EA Weight	0.49
EA Width	2.6
Inner Cube	0.0
Pack Type	Box
Web Length	5.45
Web Width	2.09

#### COMPLIANCE

ADA Compliant	True
CA Regulations	T20 Exempt - Fixtures Not Regulated
CA Prop 65	Lead
CA Status	Lawful for sale in California
FCC Compliant	True
IP Rating	IP65
Location Rating	Wet
Safety Listing	Not Applicable
CA Compliance Text	Lawful for sale
Title 20	Exempt
T24 Compliant	False