



Project / Job Name:

Location:

Fixture Type:

Notes:

**65-940** - Starfish; SMART Indoor Security Camera;  
White Finish



#### GENERAL

Company	NUVO
EA Height	3.74
EA Width	2.68
EA Length	3.78
Camera Resolution	Main Stream: 1080P at 20fps; Sub Stream: 640x360 at 20fps
Starfish Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Diameter	2.36
Extends (in)	2.64
Material	Plastic
Fixture Type	Security Camera
Camera Focal Length	4.0
Camera Image Compression	H.265/H.264
Camera Image Sensor	1/3 Color CMOS
Includes	Mounting Hardware and Accessories; USB A Cord; Plug Adapter; 32GB SD Card
Status	Active
Camera Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card
Camera Viewing Angle	93 D
Starfish Voice Assistants Supported	Alexa, Google Home, Siri, SmartThings
Finish Family	White
Additional Info	Video stream supported on Alexa Show devices
Amps	1.000A
Camera Audio	2-Way Communication
Has Camera	True
IOT Enabled	True
Starfish Operational Humidity	0% - 95%
Starfish Software Supported	AWS Cloud Security Servers, Tuya/Starfish App
Indoor Outdoor	Indoor
Product Technology	Not Applicable

#### ELECTRICAL

Operating Temp	-10C (+14F) to +45C (+113F)
Volts	5V

#### PHYSICAL

Finish	WHITE
--------	-------

#### ADDITIONAL INFO

Warranty	1-Year
----------	--------

#### FEATURES

Camera Night Vision	IR Distance 10m
---------------------	-----------------

#### PACKAGING

UPC	045923664595
Case Cube	1.3068
Case Height	9.25
Case Length	16.54
Case Quantity	40
Case UPC	10045923664592
Case Weight	16.95
Case Width	14.76
EA Cube	0.0219
EA Height	3.74
EA Length	3.78
EA Quantity	1
EA Weight	0.14
EA Width	2.68
Inner Cube	0.0
Pack Type	Box

#### COMPLIANCE

ADA Compliant	True
CA Regulations	T20 Exempt - Fixtures Not Regulated
CA Prop 65	Lead
CA Status	Lawful for sale in California
FCC Compliant	True
Safety Listing	cULus
CA Compliance Text	Lawful for sale
Title 20	Exempt
T24 Compliant	False