



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 3-Pole, 240VAC are Circuit Protection Molded Case Circuit Breakers. Type: HBL Application: Electrical Distribution Standard: UL 489 Voltage Rating: 240V Amperage Rating: 80A Trip Range: Thermal Magnetic Interrupt Rating: 65 AIC Number Of Poles: 3P

product function note	
number of poles	3
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	80 A
Model	
product brand name	Siemens
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	3 in
design of the product	HBL
height [in]	4 in
width [in]	3 in
General product approval	
standard	UL 489

last modified:

12/20/2023 

