






- FINGER GUARDS OPTIONAL
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 0V H2 480 440 H3 600 575 550 HV TERMINAL LOCATION MADE IN MEXICO SN	252L E50394 PDG12 TYPE 3AH LR3902 TYPE 3AH 	H1 H2 H3 hps CONTROL TRANSFORMER P/N C2G0050ACP 50 VA X4 X2 X3 X1 GND 	hps P/N C2G0050ACP 50 VA 60 Hz 130°C CLASS 252L E50394 PDG12 TYPE 3AH LR3902 TYPE 3AH 	LV TERMINAL LOCATION <table border="1"> <tr> <td>120</td> <td>240</td> </tr> <tr> <td>115</td> <td>230</td> </tr> <tr> <td>110</td> <td>220</td> </tr> <tr> <td>X4</td> <td>X2</td> </tr> <tr> <td>X3</td> <td>X1</td> </tr> <tr> <td></td> <td>GND</td> </tr> </table>	120	240	115	230	110	220	X4	X2	X3	X1		GND
120	240															
115	230															
110	220															
X4	X2															
X3	X1															
	GND															

NOTES:



TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0050ACP

1.1 jwen 2025/09/22 10:19

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.