



- FINGER GUARDS OPTIONAL
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 0V H2 480 460 440 H3 600 575 550 HV TERMINAL LOCATION MADE IN MEXICO SN	 LR3902 TYPE 3AH	 CONTROL TRANSFORMER P/N C2G0100ACP 100 VA X4 X2 X3 X1 GND	252L E50394 PDG12 TYPE 3AH LISTED LR3902 TYPE 3AH	P/N C2G0100ACP 100 VA 60 Hz 130°C CLASS 252L E50394 PDG12 TYPE 3AH LISTED LR3902 TYPE 3AH	LV TERMINAL LOCATION <table border="1"> <tr> <td>120</td> <td>240</td> </tr> <tr> <td>115</td> <td>230</td> </tr> <tr> <td>110</td> <td>220</td> </tr> <tr> <td>X4</td> <td>X2 X3 X1 GND</td> </tr> </table>	120	240	115	230	110	220	X4	X2 X3 X1 GND
120	240												
115	230												
110	220												
X4	X2 X3 X1 GND												

NOTES:

hammond
POWER SOLUTIONS

TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0100ACP

1.1 jwen 2025/09/22 10:19

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.