



- FINGER GUARDS OPTIONAL
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 0V	H2 480 460 440	H3 600 575 550	hps	hps	CONTROL TRANSFORMER P/N C2G0150ACP 150 VA	252L E50394 PDG12 TYPE 3AH	LISTED LR3902 TYPE 3AH	P/N C2G0150ACP 150 VA 60 Hz 130°C CLASS	252L E50394 PDG12 TYPE 3AH	LISTED LR3902 TYPE 3AH	LV TERMINAL LOCATION 120 240 115 230 110 220	X4 X2 X3 X1 GND
----------	-------------------------	-------------------------	-----	-----	---	-------------------------------------	------------------------------	---	-------------------------------------	------------------------------	---	--------------------

NOTES:



TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0150ACP

1.1 jwen 2025/09/22 10:19

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.