







- FINGER GUARDS FOR TERMINAL BLOCKS AND FUSING OPTIONAL
- OPTIONAL FUSE CLIPS WILL ADD 0.35"[9mm] TO HEIGHT
- OPTIONAL FUSE CLIPS WITH FINGER GUARDS WILL ADD 0.48"[12mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 0V H2 480 460 440 H3 600 575 550 HV TERMINAL LOCATION MADE IN MEXICO SN	 LR3902 TYPE 3AH	 T1 T2 X1 X2 X3 X4	CONTROL TRANSFORMER P/N C2G0500ACP 500 VA 252L E50394 PDG12 TYPE 3AH LISTED LR3902 TYPE 3AH	LV TERMINAL LOCATION <table border="1"> <tr> <td>120</td> <td>240</td> </tr> <tr> <td>115</td> <td>230</td> </tr> <tr> <td>110</td> <td>220</td> </tr> <tr> <td>X4</td> <td>X2</td> </tr> <tr> <td>X3</td> <td>X1</td> </tr> <tr> <td></td> <td>GND</td> </tr> </table>	120	240	115	230	110	220	X4	X2	X3	X1		GND
120	240															
115	230															
110	220															
X4	X2															
X3	X1															
	GND															

NOTES:



TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0500ACP