






- FINGER GUARDS FOR TERMINAL BLOCKS AND FUSING OPTIONAL
- OPTIONAL FUSE CLIPS WILL ADD 0.31"[9mm] TO HEIGHT
- OPTIONAL FUSE CLIPS WITH FINGER GUARDS WILL ADD 0.44"[11mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 0V H2 480 450 440 H3 600 575 550 HV TERMINAL LOCATION hps MADE IN MEXICO SN 252L E50394 PDG12 TYPE 3AH	TH X1 X2 X3 H2 H3	LISTED 252L E50394 PDG12 TYPE 3AH hammond POWER SOLUTIONS CONTROL TRANSFORMER P/N C2G1000ACP 1000 VA T2 T1 X4 X2 X3 X1 GND	LISTED 252L E50394 PDG12 TYPE 3AH LV TERMINAL LOCATION X4 X2 X3 X1 GND
---	--	---	--

NOTES:

hammond
POWER SOLUTIONS

TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G1000ACP

1.1 jwen 2025/09/22 10:20

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.