

INSULATION RESISTANCE TESTER

Test up to 4000MΩ at 125V, 250V, 500V, and 1000V DC



Stand For Hands-Free Operation



ET600 Includes:

- Owner's Manual
- Carrying Case
- Right Angle Test Leads
- Heavy-duty Alligator Test Leads
- 6 x AA Batteries

Measurement	ET600
Test Voltages	125V, 250V, 500V, 1000V
Insulation Resistance	4000MΩ
Test Lock	●
Live Circuit Detection	●
AC/DC Voltage	1000V
Resistance	400kΩ
True RMS	●
Audible Continuity	●
Backlight	●
Auto-Ranging	●
Auto-Zero	●
Data Hold	●
Max/Min Value	●
Auto Power-Off	●
LCD Display Count	4000
Bar Graph	●
Over-Range Indication	●
Durability	
Safety Rating	CAT IV 600V CAT III 1000V

Cat. No.	UPC#	Description	Dimensions
ET600	0-92644-69242-0	Insulation Resistance Tester	7.93" L x 3.59" W x 2.32" H (210.5 x 91.2 x 58.9 mm)
Accessories and Replacement Parts			
69417	0-92644-69417-2	Magnetic Hanger (Clips securely into back of ET600)	
69410	0-92644-69410-3	Replacement Right Angle Test Lead Set (One pair of universal test leads and one set of alligator clips)	
69420	0-92644-69295-6	Replacement Heavy Duty Alligator Test Leads (One pair of heavy-duty test leads)	

⚠ Visit www.kleintools.com for warnings and instructions.

See our complete line of Test & Measurement Products. • www.kleintools.com



CAT IV
600V

CAT III
1000V



© 2025 Klein Tools, Inc. • Lincolnshire, IL 60069 • Rev. B • 11/25