



- FINGER GUARDS OPTIONAL
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 220 230 240 1 3 2 4 HV TERMINAL LOCATION MADE IN MEXICO SN	H3 440 460 480 1 3 2 4 HV TERMINAL LOCATION MADE IN MEXICO SN	H2 440 460 480 1 3 2 4 HV TERMINAL LOCATION MADE IN MEXICO SN	H4 440 460 480 1 3 2 4 HV TERMINAL LOCATION MADE IN MEXICO SN	252L E50394 PDG12 TYPE 3AH LISTED LR3902 TYPE 3AH	hps	hps	CONTROL TRANSFORMER P/N C2G0050MQMJ 50 VA X4 X2 X3 X1 GND	252L E50394 PDG12 TYPE 3AH LISTED LR3902 TYPE 3AH	hps	P/N C2G0050MQMJ 50 VA 50/60 Hz 130°C CLASS LISTED 252L E50394 PDG12 TYPE 3AH LISTED LR3902 TYPE 3AH	LV TERMINAL LOCATION 120 240 115 230 110 220 X4 X2 X3 X1 GND
--	--	--	--	---	-----	-----	--	---	-----	---	---

NOTES:

hammond
POWER SOLUTIONS

TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0050MQMJ

1.1 jwen 2025/09/22 10:25

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.