



- FINGER GUARDS OPTIONAL
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 220 230 240	H3 440 460 480	H2 440 460 480	H4 440 460 480	hps	hps	CONTROL TRANSFORMER P/N C2G0100QMJ 100 VA	252L E50394 PDG12 TYPE 3AH	LISTED LR3902 TYPE 3AH	P/N C2G0100QMJ 100 VA 50/60 Hz 130°C CLASS	252L E50394 PDG12 TYPE 3AH	LV TERMINAL LOCATION 120 240 115 230 110 220	X4 X2 X3 X1 GND
-------------------------	-------------------------	-------------------------	-------------------------	-----	-----	---	-------------------------------------	------------------------------	--	-------------------------------------	---	-----------------

NOTES:

hammond
POWER SOLUTIONS

TITLE: 1 PHASE GENERAL PURPOSE CONTROL TFX

1	25/09/16	RH	UPDATED EDB	DES: MSARAF
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 1

EDBC2G0100QMJ

1.1 jwen 2025/09/22 10:25

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES.