







- FINGER GUARDS FOR TERMINAL BLOCKS AND FUSING OPTIONAL
- OPTIONAL FUSE CLIPS WILL ADD 0.35"[9mm] TO HEIGHT
- OPTIONAL FUSE CLIPS WITH FINGER GUARDS WILL ADD 0.48"[12mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WILL ADD 1.3"[33mm] TO HEIGHT
- OPTIONAL FUSE BLOCK WITH FINGER GUARD WILL ADD 1.5"[38mm] TO HEIGHT
- TOLERANCES STD. +/- 0.1"[+/-3mm]
- ALL DIMENSIONS ARE IN INCHES [mm]

H1 H3 H2 H4 110 220 115 230 120 240 HV TERMINAL LOCATION 1 3 2 4 1 3 2 4 LR3902 TYPE 3AH MADE IN MEXICO SN			hps CONTROL TRANSFORMER P/N C2G0500PR 500 VA T2 T1 X2 X1 GND	 LISTED 252L E50394 PDG12 TYPE 3AH LR3902 TYPE 3AH	P/N C2G0500PR 500 VA 50/60 Hz 130°C CLASS	 LISTED 252L E50394 PDG12 TYPE 3AH	LV TERMINAL LOCATION 24 0V 23 22 X2 X1 GND
---	--	--	---	---	--	---	---

NOTES: