

Project Name

Location

Prepared By



SATCO S11293R1

9WLED/GBL/4/RGBTW/WH

Notes

[www] 10-27-2023 09:20:49

General

Status	Active
Wattage	9W
Voltage	120V-277V
Finish	White
CCT (Kelvin)	2700K-5000K
Color Temperature	RGB and Tunable White
Lumen Output	750L
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Beam Angle	36
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App

Dimensions

Width (in.)	4.92
Height (in.)	1.44
Weight (lb.)	0.99

Compliance

Safety Listing	cETLus
Location Rating	Damp
ENERGY STAR	Pending
Air Tight Rated	Yes
IC Rated	Yes
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5-Years
----------	---------