

Project Name

Location

Prepared By



SATCO S11190

24FT/LED/SL/S14/SF/RGBTW/120V

Notes

(www) 18-27-2023 05:20:49

General

Status	Active
Finish	Black
Wattage	7W
CCT (Kelvin)	3000K-6500K
Color Temperature	RGB and Tunable White
Indoor or Outdoor Fixture	Indoor and Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	No
Operational Humidity	30% - 70%
Life Cycles	100000
Software Upgradeable	Yes
Communication Protocol	WiFi-2.4GHz
Voice Assistants Supported	Alexa; Google Home; Siri; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	83
Lumen Output	340L
Rated Hours	30000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	320
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	3.51
Fixture Material	PVC
Fixture Type	String Light
Max. Connectable Units	5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class A

Additional Information

Warranty	1-Year
----------	--------