

Project Name

Location

Prepared By



## SATCO S8020R1

24FT/LED/SL/S14/27K/120V

### Notes

(www) 18-27-2023 05:20:50

### General

Status	Active
Finish	Black
Wattage	12W
CCT (Kelvin)	2700K
Color Temperature	Warm White
Indoor or Outdoor Fixture	Indoor and Outdoor

### Smart Product Info

IOT Enabled	No
Integrated Camera	No

### Specifications

Technology	LED
CRI	84
Lumen Output	800L
Rated Hours	30000
Voltage	120V
Dimmable	Non-Dimmable
Beam Angle	320
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	3.51
Fixture Material	PVC
Fixture Type	String Light
Max. Connectable Units	40

### Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

### Additional Information

Warranty	1-Year
----------	--------